



Full Circle® Wide Range Repair Clamp

All Stainless Steel, Fabricated Lugs, Single Band

281



THIS PRODUCT DOES NOT RESTRAIN PIPE MOVEMENT. Proper anchoring is required to prevent pipe pull-out. Failure to anchor or improper anchoring can result in dangerous pipe content escape, property damage, serious injury, or death. Read product installation instructions prior to installing this product.

Description: A wide range repair clamp with double the range of Smith-Blair's standard 261 repair clamp delivering the convenience of handling more applications with fewer product sizes.

Application: The repair of leaks due to complete breaks, splits, holes or for joining pipes of the same diameter.

Key Features:

- Up to .95" range
- Widest range repair clamp in the Smith-Blair's product line
- Can be used to repairs pipes or join pipe ends
- All 304 Stainless Steel construction for corrosion resistance
- A 360° Gasket seal provides maximum support and reinforcement
- Keeper bar helps pull clamp around the pipe and closes the clamp during installation
- Standard widths 7.5", 10.0", 12.5", 15.0", 20.0", 25.0", 30.0"

Materials Specifications (subject to change):

BAND: Type 304 Stainless Steel per ASTM A240

FINGER: Type 304 Stainless Steel, per ASTM A 240

LUG BAR: Type 304 Stainless Steel per ASTM A 240

KEEPER BAR: Type 304 Stainless Steel per ASTM 240

NUTS: Type 316 Stainless Steel GR 8 per ASTM A194, Fluoropolymer coated

WASHER: Type 304 Stainless Steel per ASTM A 240

STUD: Type 304 Stainless Steel per ASTM A276; epoxy coated to minimize galling

GASKET: Nitrile (Buna N) per ASTM D2000

Working Pressure: Up to 150 PSI

Pipe Applications: Carbon Steel, Stainless Steel, Ductile Iron, PVC, Asbestos Cement, Copper Aluminum.

Sizes (in inches): 3" to 12" nominal