



a xylem brand

CURVE:

PUMP: 8X6X15F 8150

SPEED: 2950 RPM

IMPELLER DATA

1500 GPM FIRE PUMP APPROVAL PRESSURE RANGE UL/FM: 123-259 PSI

IMP : **AC6088**

NO OF : **4**
VANES

MAX : **14.5"** DIA

MIN : **10.75"** DIA

MAX : **0.93"**
SPHERE

INLET : **37.3"**
AREA

