




4DWC Simplex NSS34865

Control Panel Schematic and Layout

DRAWING
BGNSS34865 R1

CONTROL PANEL SCHEMATIC






CONTROL PANEL SCHEMATIC

BGNSS34865 R1

FNAME: NSS34865

REVDATE: 0423




MULTI-TAP TRANSFORMER:
CONNECT FACTORY TAGGED WIRES TO APPROPRIATE TRANSFORMER VOLTAGE TAP. SEE BELOW FOR CONNECTIONS:
FOR 208V OPERATION, CONNECT TO FUSE INPUT HF & TO TRANSFORMER TAP H2.
FOR 240V OPERATION, CONNECT TO FUSE INPUT HF & TO TRANSFORMER TAP H3.
FOR 480V OPERATION, CONNECT TO FUSE INPUT HF & TO TRANSFORMER TAP H4.

----- DASHED LINE INDICATES FIELD WIRING.
USE COPPER CONDUCTORS ONLY.
TEMPERATURE RATING OF CONDUCTORS IS TO BE: 60°C (140°F) FOR UNDER 100A, 75°C (167°F) FOR OVER 100A.
BRANCH CIRCUIT PROTECTION SHALL BE PROVIDED BY THE INSTALLER; MUST BE SIZED ACCORDING TO PUMP/MOTOR MANUFACTURING SPECIFICATIONS.
VERIFY CORRECT OPERATION OF CONTROL PANEL AFTER INSTALLATION IS COMPLETE.

FIELD WIRING TORQUE SPECS.		DRAWN BY: AL		DATE: 04/10/23	
TERMINAL BLOCK UT 2.5	5 IN-LB	APPROVED BY: DO		DATE: 04/11/23	
TERMINAL BLOCK UT 4	7 IN-LB	THIS DRAWING CONTAINS PROPRIETARY INFORMATION AND SHALL NOT BE USED OR DISCLOSED WITHOUT PRIOR WRITTEN AUTHORIZATION.			
TERMINAL BLOCK UT 6	15 IN-LB				
TERMINAL BLOCK UT 10	15 IN-LB				
TERMINAL BLOCK UT 16	25 IN-LB				
TERMINAL BLOCK UT 35	30 IN-LB				
TS1, TS2, J2 & J3 PCB	5 IN-LB	TITLE: NSS34865 CONTROL PANEL SCHEMATIC			
TRANSFORMER H1F, H2F & H3F	15 IN-LB	SIZE B		DWG NO. 4212	
TRANSFORMER H1, H2 & H3	10 IN-LB	PART NO.		NSS34865	
DS1 VLS3P16-63 R1	16 IN-LB	SCALE NONE		SHEET 2 OF 2	
DS1 VLS3P63-125 R2	45 IN-LB				
DS1 LK4JU3CN 100A	36 IN-LB				
DS1 LK4MU3N 200A	200 IN-LB				

FNAME: NSS34865

REVDATE: 0423



DRAWN BY:	AL	DATE:	04/10/23			
APPROVED BY:	DO	DATE:	04/11/23			
THIS DRAWING CONTAINS PROPRIETARY INFORMATION AND SHALL NOT BE USED OR DISCLOSED WITHOUT PRIOR WRITTEN AUTHORIZATION.				TITLE:		
				NSS34865		
				CONTROL PANEL LAYOUT		
SIZE	B	DWG NO.	4213	PART NO.	NSS34865	REV
SCALE	NONE			SHEET	1	OF 2

CONTROL PANEL LAYOUT

FNAME: NSS34865

REVDATE: 0423

QTY	MANUFACTURER	DESCRIPTION	PART NUMBER	REF.
1	Integra	P.C. Nema 4X Enclosure 18x16x10	H181610HCLL	E1
1	All-Spec	Dead Front	624P	DF1
1	All-Spec	Back Panel	625	BP1
1	Integra	Hinge Kit	US0PK-P909	N/A
1	Ingram	Beacon	R10-SM	BE1
1	Ingram	Buzzer	PB-024-AD	B1
1	VCC	Red Light 125V	1050QC1	LT1
1	See Water	Display Board	GBJ5	GBJ5
3	LEDTRONICS	White Lense	LENS-LCD780-CWF	N/A
2	See Water	Flat Cable Assembly	IDC-25MB	N/A
2	Molex	4 Pin Connector	09-50-3041	N/A
1	Molex	6 Pin Connector	09-50-3061	N/A
1	See Water	Power Circuit Board	WWD	PCB1
1	Carling	HOA Toggle Switch	6FC57-73	TG1
1	Schneider	Multitap Transformer 50VA	9070TF50D20	XF1
2	Mersen	ATQR 3/10A Fuse	ATQR-3/10A	XF1
1	Mersen	TRM 6/10A Fuse	TRM-6/10A	XF1
1	Schneider	Motor Protector	GV3P65	MP1
1	Schneider	Side Mount Auxilliary	GVAN11	OL1

QTY	MANUFACTURER	DESCRIPTION	PART NUMBER	REF.
1	Schneider	Contactora	LC1D65AG7	M1
1	Noark	Circuit Breaker 3A 1 Pole	B1E1C3	CB1
1	Schneider	Mini Plug In Relay Holder	RSZE1S35M	CR1
1	Schneider	Mini Plug In Relay Clamp	RSZR215	CR1
1	Schneider	Mini Plug In Relay 12VDC	RSB1A120JD	CR1
1	Macromatics	Seal Fail Dual Channel Relay	SFP120C100	SFR1
1	Macromatics	8 Pin Socket	70169-D	SFR1
1	Trumeter	Elapsed Time Meter	6320-2500-0000	ETM1
1	Trumeter	Cycle Counter	6300-2500-0000	CC1
2	Phoenix Contact	Terminal Block UT-4	3044102	TB2
3	Phoenix Contact	Terminal Block UT-16	3044199	TB1
1	Phoenix Contact	Terminal Block UT-16-PE	3044212	G1-2
7	Phoenix Contact	End Stop	3022218	N/A
2	Phoenix Contact	End Cover UT-2.5-10	3047028	N/A
1	Phoenix Contact	End Cover UT-16	3047206	N/A
1	Burndy	Ground	6T	G2
4	Altech	Angled Mounting Bracket	CA603	N/A
3	See Water	N.O. Narrow Angle Floats 50'	FPCON50	N/A
1	UL	508A UL Label	N/A	N/A

DRAWN BY:	AL	DATE:	04/10/23			
APPROVED BY:	DO	DATE:	04/11/23			
THIS DRAWING CONTAINS PROPRIETARY INFORMATION AND SHALL NOT BE USED OR DISCLOSED WITHOUT PRIOR WRITTEN AUTHORIZATION.				TITLE:		
				NSS34865		
				CONTROL PANEL LAYOUT		
SIZE	B	DWG NO.	4213	PART NO.	NSS34865	
SCALE	NONE				SHEET	2 OF 2



Xylem Inc.
2881 East Bayard Street Ext.
Seneca Falls, NY 13148
Phone: (800) 453-6777
Fax: (888) 322-5877
www.xylem.com/bellgossett