

# 3888 3WDA

## PUMP TO PANEL PART NUMBERS

| Pump      | HP  | Phase | Voltage | Amps | Simplex Panel | Duplex Panel |
|-----------|-----|-------|---------|------|---------------|--------------|
| 3WDA1518M | 1.5 | 1     | 208     | 15   | C4S10020      | C4D10020     |
| 3WDA1512M | 1.5 | 1     | 230     | 12.5 | C4S10020      | C4D10020     |
| 3WDA1538M | 1.5 | 3     | 200     | 11.5 | C4S31016      | C4D31016     |
| 3WDA1532M | 1.5 | 3     | 230     | 10   | C4S31016      | C4D31016     |
| 3WDA1534M | 1.5 | 3     | 460     | 5    | C4S34063      | C4D34063     |
| 3WDA1537M | 1.5 | 3     | 575     | 4    | C4S34063      | C4D34063     |
| 3WDA1518  | 1.5 | 1     | 208     | 15   | C4S10020      | C4D10020     |
| 3WDA1512  | 1.5 | 1     | 230     | 12.5 | C4S10020      | C4D10020     |
| 3WDA1538  | 1.5 | 3     | 200     | 11.5 | C4S31016      | C4D31016     |
| 3WDA1532  | 1.5 | 3     | 230     | 10   | C4S31016      | C4D31016     |
| 3WDA1534  | 1.5 | 3     | 460     | 5    | C4S34063      | C4D34063     |
| 3WDA1537  | 1.5 | 3     | 575     | 4    | C4S34063      | C4D34063     |
| 3WDA2018  | 2   | 1     | 208     | 19   | C4S10020      | C4D10020     |
| 3WDA2012  | 2   | 1     | 230     | 16   | C4S10020      | C4D10020     |
| 3WDA2038  | 2   | 3     | 200     | 11.5 | C4S31016      | C4D31016     |
| 3WDA2032  | 2   | 3     | 230     | 10   | C4S31016      | C4D31016     |
| 3WDA2034  | 2   | 3     | 460     | 5    | C4S34063      | C4D34063     |
| 3WDA2037  | 2   | 3     | 575     | 4    | C4S34063      | C4D34063     |
| 3WDA3018  | 3   | 1     | 208     | 25.5 | C4S12136      | C4D12127     |
| 3WDA3012  | 3   | 1     | 230     | 21.5 | C4S12136      | C4D12127     |
| 3WDA3038  | 3   | 3     | 200     | 15.2 | C4S31016      | C4D31016     |
| 3WDA3032  | 3   | 3     | 230     | 12   | C4S31016      | C4D31016     |
| 3WDA3034  | 3   | 3     | 460     | 6    | C4S34063      | C4D34063     |
| 3WDA3037  | 3   | 3     | 575     | 4.8  | C4S34063      | C4D34063     |
| 3WDA5012  | 5   | 1     | 230     | 26.5 | C4S12136      | C4D12836     |
| 3WDA5038  | 5   | 3     | 200     | 18.8 | C4S31620      | C4D31620     |
| 3WDA5032  | 5   | 3     | 230     | 16.4 | C4S31620      | C4D31620     |
| 3WDA5034  | 5   | 3     | 460     | 8.2  | C4S36310      | C4D36310     |
| 3WDA5037  | 5   | 3     | 575     | 6.8  | C4S36310      | C4D36310     |