

G70 SERIES AIR OPERATED DIAPHRAGM PUMP

Model No.	Max Flow GPM (LPM)	Diaphragm	Check Valve			Liquid IN	Liquid OUT	Gas Inlet Fitting	Body Material	Compliance
			Body	Seal / O-Ring	Spring					
G70C162	5 (19)	FFKM	PP / PP	Viton Extreme	Hastelloy	3/8 ST HB (10-13mm)	3/8 ST HB (10-13mm)	1/4 HB Strt	CF PP	ATEX
G70C202	5 (19)	FFKM	PP / PP	Viton Extreme	Hastelloy	3/8 ST HB (10-13mm)	3/8 ST HB (10-13mm)	1/4 HB Strt	CF PP	ATEX
G70C222	5 (19)	FFKM	PP / PP	Viton Extreme	Hastelloy	3/4 STRAIGHT HB	3/4 STRAIGHT HB	1/4 HB Strt	CF PP	ATEX
G70K162	5 (19)	FFKM	Nylon / Nylon	Viton Extreme	Hastelloy	3/8 ST HB (10-13mm)	3/8 ST HB (10-13mm)	1/4 HB Strt	CF PP	ATEX
G70K202	5 (19)	FFKM	Nylon / Nylon	Viton Extreme	Hastelloy	3/8 ST HB (10-13mm)	3/8 ST HB (10-13mm)	1/4 HB Strt	CF PP	ATEX
G71K002	5 (19)	FFKM	Nylon / Nylon	Viton Extreme	Hastelloy	None	None	1/4 HB Strt	GF Nylon Caps	ATEX