

4053 Arsenic Test Kit

Fast, Easy, and Reliable Arsenic Test Kit



Description


The popular 4053 Arsenic Test Kit is essential for monitoring ground and surface water sources for arsenic contamination. This easy to use kit includes diagrammed instructions and distinct color standards for fast and accurate results. The testing procedure detects inorganic As^{+3} and As^{+5} by converting these to arsine gas, which produces a yellow to brown color on a test strip. The strip is then compared to color standards to determine the arsenic concentration. The kit contains enough materials to do 50 tests.

The test kit is accurate for the following ranges (ppb): 4, 6, 8, 10, 12, 14, 16, 18, 20, 30, 40, 50, 60, 70, 80, 100, 140, 160. It includes a sulfide interference remover for up to 2 ppm.

Features

- Fast, easy, accurate
- Unique design eliminates hazmat fees
- Low range sensitivity

Applications



Ideal for examining water quality in surface water or groundwater.

Ordering & Options

Order No.	Description
4053	Arsenic Test Kit



In the U.S. call toll free
at 1-800-876-1172
International: 1-979-690-5560
Fax: 1-979-690-0440
Email: globalw@globalw.com

Visit our online catalog at:
www.globalw.com
Our Address:
11390 Amalgam Way
Gold River, CA 95670