



PH100 Handheld pH Meter



- Flat Surface Electrode
- Replacement indicator
- Calibration indicator
- Saves up to 15 readings
- Analog bar graph

Description

The PH100 Handheld pH Meter features a unique flat surface electrode that provides fast and easy on the spot pH measurements of liquids, semi-solids, and solids. The design is rugged and designed for harsh environments, so you no longer have to worry about electrode breakage or clogged junctions. The handheld pH Meter offers a RENEW indicator that tells you when it is time to replace the handheld pH meter's electrode. The handheld pH meter also features a CALIBRATION indicator that indicates when the pH meter needs to be recalibrated.

The PH100 Handheld pH Meter is IP67 rated for wet environments. The pH meter can save up to 15 sequentially tagged readings in its memory, which allows detection of changes over time. The pH meter also, has an analog bar graph originating at the neutral point (pH 7.00) to conveniently view trends in acidity or alkalinity. The handheld pH meter is temperature compensated and will display the current temperature.

Specifications

Range: 0.00-14.00 pH
Temperature: 23° to 194°F (-5° to +90°C)
Max. Resolution: 0.01pH, 0.1°
Accuracy: ±0.01pH, ±1.8°F/1°C
Power: four LR44 button batteries
Size: 1.4x6.8x1.6" (35.6x172.7x40.6mm)
Weight: 3.8oz (110g)

Price List

PH100

Handheld pH Meter.....\$89

PH105

Spare pH Meter Electrode Module.....\$39

CA895

Carrying Case, Small with Belt Loop.....\$25

Contact
Global Water
for all your
instrumentation
needs:

Water Level

Water Flow

Water Samplers

Water Quality

Weather

Remote Monitoring

Control



Global Water
The Leader in Water Instrumentation

In the U.S. call toll free
at 1-800-876-1172
International: 916-638-3429
Fax: 916-638-3270
Email: globalw@globalw.com

Visit our online catalog at:
www.globalw.com
Our Address:
11390 Amalgam Way
Gold River, CA 95670