

RS Series vs. Grizzly 4" Submersible Pumps Red Jacket Series

This cross-reference tool helps customers, distributors, and technical teams transition from the legacy Red Jacket Grizzly Series to the Goulds Water Technology Red Jacket RS Submersible Pump. By comparing hydraulic performance curves, the closest RS Submersible Pump equivalent can be identified, ensuring confident selection of an RS model that meets or exceeds the legacy Grizzly pump's performance.



Grizzly Part Number	Description	RS Series Cross	Description
6G17	1/2HP 17STG LIQUID END GRIZ	5RS05	1/2HP WET END 12STG
6G19	3/4HP 19STG LIQUID END GRIZ	5RS07	3/4HP WET END 15STG
6G24	1HP 24STG LIQUID END GRIZ	5RS10	1HP WET END 20STG
8G12	1/2HP 12STG LIQUID END GRIZ	7RS05	1/2HP WET END 10STG
8G16	3/4HP 16STG LIQUID END GRIZ	7RS07	3/4HP WET END 13STG
8G21	1HP 21STG LIQUID END GRIZ	7RS10	1HP WET END 17STG
8G25	1.5HP 25STG LIQUID END GRIZ	NO REPLACEMENT	-
12G8	1/2HP 8STG LIQUID END GRIZ	10RS05	1/2HP WET END 10STG
12G9	1/2HP 9STG LIQUID END GRIZ	10RS05	1/2HP WET END 10STG
12G12	3/4HP 12STG LIQUID END GRIZ	10RS07	3/4HP WET END 14STG
12G14	1HP 14STG LIQUID END GRIZ	10RS10	1HP WET END 16STG
12G18	1.5HP 18STG LIQUID END GRIZ	10RS15	1.5HP WET END 17STG
20G5	1/2HP 5STG LIQUID END GRIZ	18RS07	3/4HP WET END 6STG
20G6	3/4HP 6STG LIQUID END GRIZ	18RS07	3/4HP WET END 6STG
20G8	1HP 8STG LIQUID END GRIZ	18RS10	1HP WET END 8STG
20G11	1.5HP 11STG LIQUID END GRIZ	18RS15	1.5HP WET END 11STG
25G7	1HP 7STG LIQUID END GRIZ	25RS10	1HP WET END 7STG
25G10	1.5HP 10STG LIQUID END GRIZ	25RS15	1.5HP WET END 9STG
50C20112G8	1/2HP 1/60/115 2W 8STG GRIZ	10RS05421C	1/2HP 1/60/115 2W 10STG 4"SUB
50C20112G9	1/2HP 1/60/115 2W 9STG GRIZ	10RS05421C	1/2HP 1/60/115 2W 10STG 4"SUB
50C20120G5	1/2HP 1/60/115 2W 5STG GRIZ	NO REPLACEMENT	-
50C2016G17	1/2HP 1/60/115 2W 17STG GRIZ	5RS05421C	1/2HP 1/60/115 2W 12STG 4"SUB
50C2018G12	1/2HP 1/60/115 2W 12STG GRIZ	7RS05421C	1/2HP 1/60/115 2W 10STG 4"SUB
50C21112G8	1/2HP 1/60/230 2W 8STG GRIZ	10RS05422C	1/2HP 1/60/230 2W 10STG 4" SUB
50C21112G9	1/2HP 1/60/230 2W 9STG GRIZ	10RS05422C	1/2HP 1/60/230 2W 10STG 4" SUB
50C21120G5	1/2HP 1/60/230 2W 5STG GRIZ	18RS07422C	3/4HP 1/60/230 2W 6STG 4"SUB
50C2116G17	1/2HP 1/60/230 2W 17STG GRIZ	5RS05422C	1/2HP 1/60/230 2W 12STG 4"SUB
50C2118G12	1/2HP 1/60/230 2W 12STG GRIZ	7RS05422C	1/2HP 1/60/230 2W 10STG 4"SUB
50C30112G8	1/2HP 1/60/115 3W 8STG GRIZ	10RS05411C	1/2HP 1/60/115 3W 10STG 4"SUB
50C30112G9	1/2HP 1/60/115 3W 9STG GRIZ	10RS05411C	1/2HP 1/60/115 3W 10STG 4"SUB

Grizzly Part Number	Description	RS Series Cross	Description
50C30120G5	1/2HP 1/60/115 3W 5STG GRIZ	NO REPLACEMENT	-
50C3016G17	1/2HP 1/60/115 3W 17STG GRIZ	5RS05411C	1/2HP 1/60/115 3W 12STG 4"SUB
50C3018G12	1/2HP 1/60/115 3W 12STG GRIZ	7RS05411C	1/2HP 1/60/115 3W 10STG 4"SUB
50C31112G8	1/2HP 1/60/230 3W 8STG GRIZ	10RS05412C	1/2HP 1/60/230 3W 10STG 4"SUB
50C31112G9	1/2HP 1/60/230 3W 9STG GRIZ	10RS05412C	1/2HP 1/60/230 3W 10STG 4"SUB
50C31120G5	1/2HP 1/60/230 3W 5STG GRIZ	18RS07412C	3/4HP 1/60/230 3W 6STG 4"SUB
50C3116G17	1/2HP 1/60/230 3W 17STG GRIZ	5RS05412C	1/2HP 1/60/230 3W 12STG 4"SUB
50C3118G12	1/2HP 1/60/230 3W 12STG GRIZ	7RS05412C	1/2HP 1/60/230 3W 10STG 4"SUB
75C21112G12	3/4HP 1/60/230 2W 12STG GRIZ	10RS07422C	3/4HP 1/60/230 2W 14STG 4"SUB
75C21120G6	3/4HP 1/60/230 2W 6STG GRIZ	18RS07422C	3/4HP 1/60/230 2W 6STG 4"SUB
75C2116G19	3/4HP 1/60/230 2W 19STG GRIZ	5RS07422C	3/4HP 1/60/230 2W 15STG 4"SUB
75C2118G16	3/4HP 1/60/230 2W 16STG GRIZ	7RS07422C	3/4HP 1/60/230 2W 13STG 4"SUB
75C31112G12	3/4HP 1/60/230 3W 12STG GRIZ	10RS07412C	3/4HP 1/60/230 3W 14STG 4"SUB
75C31120G6	3/4HP 1/60/230 3W 6STG GRIZ	18RS07412C	3/4HP 1/60/230 3W 6STG 4"SUB
75C3116G19	3/4HP 1/60/230 3W 19STG GRIZ	5RS07412C	3/4HP 1/60/230 3W 15STG 4"SUB
75C3118G16	3/4HP 1/60/230 3W 16STG GRIZ	7RS07412C	3/4HP 1/60/230 3W 13STG 4"SUB
100C21112G14	1HP 1/60/230 2W 14STG GRIZ	10RS10422C	1HP 1/60/230 2W 16STG 4"SUB
100C21120G8	1HP 1/60/230 2W 8STG GRIZ	18RS10422C	1HP 1/60/230 2W 8STG 4"SUB
100C21125G7	1HP 1/60/230 2W 7STG GRIZ	25RS10422C	1HP 1/60/230 2W 7STG 4"SUB
100C2116G24	1HP 1/60/230 2W 24STG GRIZ	5RS10422C	1HP 1/60/230 2W 20STG 4"SUB
100C2118G21	1HP 1/60/230 2W 21STG GRIZ	7RS10422C	1HP 1/60/230 2W 17STG 4"SUB
100C31112G14	1HP 1/60/230 3W 14STG GRIZ	10RS10412C	1HP 1/60/230 3W 16STG 4"SUB
100C31120G8	1HP 1/60/230 3W 8STG GRIZ	18RS10412C	1HP 1/60/230 3W 8STG 4"SUB
100C31125G7	1HP 1/60/230 3W 7STG GRIZ	25RS10412C	1HP 1/60/230 3W 7STG 4"SUB
100C3116G24	1HP 1/60/230 3W 24STG GRIZ	5RS10412C	1HP 1/60/230 3W 20STG 4"SUB
100C3118G21	1HP 1/60/230 3W 21STG GRIZ	7RS10412C	1HP 1/60/230 3W 13STG 4"SUB
50C21112G18	1.5HP 1/60/230 2W 18STG GRIZ	10RS15422C	1.5HP 1/60/230 2W 17STG 4"SUB
150C21120G11	1.5HP 1/60/230 2W 11STG GRIZ	18RS15422C	1.5HP 1/60/230 2W 11STG 4"SUB
150C21125G10	1.5HP 1/60/230 2W 10STG GRIZ	25RS15422C	1.5HP 1/60/230 2W 9STG 4"SUB
150C2118G25	1.5HP 1/60/230 2W 25STG GRIZ	NO REPLACEMENT	-
150C31112G18	1.5HP 1/60/230 3W 18STG GRIZ	10RS15412C	1.5HP 1/60/230 3W 17STG 4"SUB
150C31120G11	1.5HP 1/60/230 3W 11STG GRIZ	18RS15412C	1.5HP 1/60/230 3W 11STG 4"SUB
150C31125G10	1.5HP 1/60/230 3W 10STG GRIZ	25RS15412C	1.5HP 1/60/230 3W 9STG 4"SUB
150C3118G25	1.5HP 1/60/230 3W 25STG GRIZ	NO REPLACEMENT	-

Xylem Inc.
2881 East Bayard Street Ext.,
Suite A
Seneca Falls, NY 13148

Phone: (866) 325-4210
Fax: (888) 322-5877
www.xylem.com/goulds

Subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

© 2025 Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are property of their respective owners.

