

3888D3

PUMP-TO-PANEL PART NUMBERS

Pump	HP	Phase	Voltage	Amps	Simplex Panel	Duplex Panel
WS1518D3M	1.5	1	208	15	C4S10020	C4D10020
WS1512D3M	1.5	1	230	12.5	C4S10020	C4D10020
WS1538D3M	1.5	3	200	11.5	C4S31016	C4D31016
WS1532D3M	1.5	3	230	10	C4S31016	C4D31016
WS1534D3M	1.5	3	460	5	C4S34063	C4D34063
WS1537D3M	1.5	3	575	4	C4S34063	C4D34063
WS1518D3	1.5	1	208	15	C4S10020	C4D10020
WS1512D3	1.5	1	230	12.5	C4S10020	C4D10020
WS1538D3	1.5	3	200	11.5	C4S31016	C4D31016
WS1532D3	1.5	3	230	10	C4S31016	C4D31016
WS1534D3	1.5	3	460	5	C4S34063	C4D34063
WS1537D3	1.5	3	575	4	C4S34063	C4D34063
WS2018D3	2	1	208	19	C4S10020	C4D12127
WS2012D3	2	1	230	16	C4S10020	C4D10020
WS2038D3	2	3	200	11.5	C4S31016	C4D31016
WS2032D3	2	3	230	10	C4S31016	C4D31016
WS2034D3	2	3	460	5	C4S34063	C4D34063
WS2037D3	2	3	575	4	C4S34063	C4D34063
WS3018D3	3	1	208	25.5	C4S12136	C4D12836
WS3012D3	3	1	230	21.5	C4S12136	C4D12127
WS3038D3	3	3	200	15.2	C4S31016	C4D31016
WS3032D3	3	3	230	12	C4S31016	C4D31016
WS3034D3	3	3	460	6	C4S34063	C4D34063
WS3037D3	3	3	575	4.8	C4S34063	C4D34063
WS5012D3	5	1	230	26.5	C4S12136	C4D12836
WS5038D3	5	3	200	18.8	C4S31620	C4D31620
WS5032D3	5	3	230	16.4	C4S31620	C4D31620
WS5034D3	5	3	460	8.2	C4S36310	C4D36310
WS5037D3	5	3	575	6.8	C4S36310	C4D36310