


<b>JOB:</b>   <b>UNIT TAG:</b> <b>ENGINEER:</b> <b>CONTRACTOR:</b>	<b>REPRESENTATIVE:</b>   <b>ORDER NO.</b> <b>SUBMITTED BY:</b> <b>APPROVED BY:</b>	<b>DATE:</b> <b>DATE:</b> <b>DATE:</b>
---	---	--



# 2-1/2-9SL

## Marlow Series 530

### Centrifugal Pumps - Base Mounted

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_

HP \_\_\_\_\_ RPM \_\_\_\_\_

VOLTS \_\_\_\_\_

CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_

ENCLOSURE \_\_\_\_\_

APPROX. WEIGHT \_\_\_\_\_

SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**

BRONZE FITTED     ALL IRON

**FEATURES**

- i-ALERT™ Condition Monitor
- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


**MAXIMUM WORKING PRESSURE**

175 psi (12 bar) W.P.  
w/ 125# ANSI flange drilling


**TYPE OF SEAL**

- 530 Standard Seal (Buna-Carbon/Ceramic)
- 530 -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- 530 -S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- 530 -D Stuffing Box construction w/ Flushed Double Mechanical Seal (EPR-Carbon/Ceramic) Requires external water source
- 530 -PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

**Note: Equipped with NEOPRENE coupling**



<b>JOB:</b>   <b>UNIT TAG:</b> <b>ENGINEER:</b> <b>CONTRACTOR:</b>	<b>REPRESENTATIVE:</b>   <b>ORDER NO.</b> <b>SUBMITTED BY:</b> <b>APPROVED BY:</b>	<b>DATE:</b> <b>DATE:</b> <b>DATE:</b>
---	---	--



# 2-1/2-9SL

## Marlow Series 530

### Centrifugal Pumps - Base Mounted

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_

HP \_\_\_\_\_ RPM \_\_\_\_\_

VOLTS \_\_\_\_\_

CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_

ENCLOSURE \_\_\_\_\_

APPROX. WEIGHT \_\_\_\_\_

SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**

BRONZE FITTED     ALL IRON

**FEATURES**

- i-ALERT™ Condition Monitor
- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


**MAXIMUM WORKING PRESSURE**

175 psi (12 bar) W.P.  
w/ 125# ANSI flange drilling

**TYPE OF SEAL**


- 530 Standard Seal (Buna-Carbon/Ceramic)
- 530 -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- 530 -S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- 530 -D Stuffing Box construction w/ Flushed Double Mechanical Seal (EPR-Carbon/Ceramic) Requires external water source
- 530 -PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

**Note: Equipped with NEOPRENE coupling**



# Marlow Series 530 2-1/2-9SL Centrifugal Pump Submittal

M-530.10A



FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	2-1/2"	11/16" (17)	7" (178)
Suction	3"	3/4" (25)	7-1/2" (191)

FLANGES ARE 125# ANSI - STANDARD

## DIMENSIONS – Inches (mm)

## STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF <sub>1</sub>	HF <sub>2</sub>	HH	HL	HM MAX	HO	HP	Y	Z
<b>"S" FRAME</b>														
145T	14-5/8 (371)	31 (787)	32-1/4 (819)	10-3/4 (273)	12-7/8 (327)	25 (635)	-	3/4 (19)	2-3/4 (70)	14-1/2 (368)	17-1/2 (445)	3 (76)	4 (102)	6 (152)
182T	14-5/8 (371)	31 (787)	33-1/4 (845)	10-3/4 (273)	12-7/8 (327)	25 (635)	-	3/4 (19)	2-3/4 (70)	16 (406)	17-1/2 (445)	3 (76)	4 (102)	6 (152)
184T	14-5/8 (371)	31 (787)	34 (864)	10-3/4 (273)	12-7/8 (327)	25 (635)	-	3/4 (19)	2-3/4 (70)	16 (406)	17-1/2 (445)	3 (76)	4 (102)	6 (152)
213T	14-5/8 (371)	34-5/8 (879)	36-1/2 (927)	10-3/4 (273)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-3/4 (70)	16-5/8 (422)	17-1/2 (445)	3 (76)	4 (102)	6 (152)
215T	14-5/8 (371)	34-5/8 (879)	38 (965)	10-3/4 (273)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-3/4 (70)	16-5/8 (422)	17-1/2 (445)	3 (76)	4 (102)	6 (152)

## "L" FRAME

254T	16 (406)	46-1/2 (1181)	46-1/8 (1172)	12 (305)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	3-7/8 (98)	18-7/8 (479)	18-3/4 (476)	5 (127)	4 (102)	6 (152)
256T	16 (406)	46-1/2 (1181)	47-7/8 (1216)	12 (305)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	3-7/8 (98)	18-7/8 (479)	18-3/4 (476)	5 (127)	4 (102)	6 (152)
284TS	16 (406)	46-1/2 (1181)	47-1/4 (1200)	13 (330)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	3-7/8 (98)	21 (533)	19-3/4 (502)	5 (127)	4 (102)	6 (152)
286TS	16 (406)	46-1/2 (1181)	48-3/4 (1238)	13 (330)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	3-7/8 (98)	21 (533)	19-3/4 (502)	5 (127)	4 (102)	6 (152)
324TS	16 (406)	46-1/2 (1181)	50-5/8 (1286)	12 (305)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	3-7/8 (98)	21 (533)	18-3/4 (476)	5 (127)	4 (102)	6 (152)
326TS	16 (406)	46-1/2 (1181)	52-3/8 (1330)	12 (305)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	3-7/8 (98)	21 (533)	18-3/4 (476)	5 (127)	4 (102)	6 (152)
364TS	16 (406)	51-3/4 (1314)	54 (1372)	13 (330)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-7/8 (98)	23-1/4 (591)	19-3/4 (502)	5 (127)	4 (102)	6 (152)

## STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF <sub>1</sub>	HF <sub>2</sub>	HH	HL	HM MAX	HO	HP	Y	Z
<b>"S" FRAME</b>														
145T	14-5/8 (371)	34-5/8 (879)	35-3/4 (908)	10-3/4 (273)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-3/4 (70)	14-1/2 (368)	17-1/2 (445)	3 (76)	4 (102)	6 (152)
182T	14-5/8 (371)	34-5/8 (879)	36-3/4 (933)	10-3/4 (273)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-3/4 (70)	16 (406)	17-1/2 (445)	3 (76)	4 (102)	6 (152)
184T	14-5/8 (371)	34-5/8 (879)	37-1/2 (953)	10-3/4 (273)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-3/4 (70)	16 (406)	17-1/2 (445)	3 (76)	4 (102)	6 (152)
213T	14-5/8 (371)	39-3/8 (1000)	40-1/8 (1019)	10-3/4 (273)	12-7/8 (327)	33-3/8 (848)	-	3/4 (19)	2-3/4 (70)	16-5/8 (422)	17-1/2 (445)	3 (76)	4 (102)	6 (152)
215T	14-5/8 (371)	39-3/8 (1000)	41-5/8 (1057)	10-3/4 (273)	12-7/8 (327)	33-3/8 (848)	-	3/4 (19)	2-3/4 (70)	16-5/8 (422)	17-1/2 (445)	3 (76)	4 (102)	6 (152)

## "L" FRAME

254T	16 (406)	51-3/4 (1314)	48-1/2 (1232)	12 (305)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-7/8 (98)	18-7/8 (479)	18-3/4 (476)	5 (127)	4 (102)	6 (152)
256T	16 (406)	51-3/4 (1314)	50-1/4 (1276)	12 (305)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-7/8 (98)	18-7/8 (479)	18-3/4 (476)	5 (127)	4 (102)	6 (152)
284TS	16 (406)	51-3/4 (1314)	49-5/8 (1260)	13 (330)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-7/8 (98)	21 (533)	19-3/4 (502)	5 (127)	4 (102)	6 (152)
286TS	16 (406)	51-3/4 (1314)	52-1/8 (1324)	13 (330)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-7/8 (98)	21 (533)	19-3/4 (502)	5 (127)	4 (102)	6 (152)
324TS	16 (406)	51-3/4 (1314)	53 (1346)	12 (305)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-7/8 (98)	21 (533)	18-3/4 (476)	5 (127)	4 (102)	6 (152)
326TS	16 (406)	51-3/4 (1314)	54-3/4 (1391)	12 (305)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-7/8 (98)	21 (533)	18-3/4 (476)	5 (127)	4 (102)	6 (152)
364TS	16 (406)	51-3/4 (1314)	56-3/8 (1432)	13 (330)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-7/8 (98)	23-1/4 (591)	19-3/4 (502)	5 (127)	4 (102)	6 (152)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.  
 8200 N. Austin Avenue  
 Morton Grove, IL 60053  
 Phone: (847)966-3700  
 Fax: (847)965-8379  
 www.gouldswatertechnology.com



