



Simplex Agricultural Waste Control Panels

THREE PHASE

Provides automatic or manual pump operation, and three leg motor protection for three phase systems. Select panel by maximum amp draw and voltage.

Model No.	Amp Range	Volts
A232510AG	3-12	230
A230918AG	5.5-22	
A231327AG	10-40	
A432510AG	3-12	460
A430918AG	5.5-22	
A431327AG	10-40	

- Three phase, 60 Hz
- NEMA 4X enclosure standard
- Class 48, NEMA Rated Starter with ESP200 solid-state, Class 5, 10, 20, 30, adjustable overloads. The ESP200 solid-state, adjustable overload also provides protection against phase-loss or single-phasing, and phase on balance.
- Hand / Off / Auto switch
- Run light
- 115V transformer for pilot circuit
- Terminal block
- Circuit breakers
- Minicas device for seal fail and high temperature

Heaters are no longer required.



**THREE PHASE
MAGNETIC STARTER**