

JABSCO ELECTRO-MAGNETIC CLUTCH PUMP MODELS

Pump Models	11860 Models	11870 Models	18330 Models	50080 Models	50200 Models	50220 Models	50270 Models	50580 Models
Body Materials	Bronze	Bronze	Bronze	Bronze	Bronze	Bronze head, cast iron bearing housing	Bronze head, cast iron bearing housing	Bronze
Impeller	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile
Wearplate	Replaceable	Replaceable	Replaceable	Replaceable	Replaceable	Replaceable	Replaceable	Replaceable
Shaft Material	Stainless steel	Stainless steel	Stainless steel	Stainless steel	Stainless steel	Stainless steel	Stainless steel	Stainless steel
Seal	Carbon/ceramic mechanical type	Carbon/ceramic mechanical type	Carbon/ceramic mechanical type	Lip type	Carbon/ceramic mechanical type	Carbon/ceramic mechanical type	Carbon/ceramic mechanical type	Carbon/ceramic mechanical type
Bearings	Twin row, ball type	Twin row, ball type	Twin row, ball type	Twin row, ball type	Twin row, ball type	Twin single row, ball type	Twin single row, ball type	Twin single row, ball type
Port Type	1" NPT	1 1/4" NPT	2" NPT	1" BSP to BS21 (DIN2999)	1 1/2" BSP to BS21 (DIN2999)	1 1/2" Flange	2" Flange or 2" BSP to BS21 (DIN2999)	1" BSP to BS21 (DIN2999) or 1" NPT
Clutch Type	Electro-magnetic 12 or 24Vdc	Electro-magnetic 12, 24 or 32Vdc	Electro-magnetic 12 or 24Vdc	Electro-magnetic 12 or 24Vdc	Electro-magnetic 12 or 24Vdc	Electro-magnetic 12 or 24Vdc	Electro-magnetic 12 or 24Vdc	Electro-magnetic 12 or 24Vdc
Pulley	178mm (7") 'A' or 'B' section	178mm (7") 'A' or 'B' section	178mm (7") 'A' or 'B' section	178mm (7") 'A' or 'B' section	178mm (7") 'A' or 'B' section	178mm (7") 'A' or 'B' section	178mm (7") 'A' or 'B' section	178mm (7") 'A' or 'B' section
Weight (lb. / kg.)	15 / 6.8	19.5 / 8.9	29 / 13.2	5-Nov	20.9 / 9.5	24.6 / 11.2	27 / 12.2	16.5 / 7.5