

JABSCO MANUAL CLUTCH PUMP MODELS

Pump Models	51080 Models	51200 Models	51220 Models	51270 Models	51580 Models
Body Materials	Bronze	Bronze	Bronze head, Cast Iron bearing housing	Bronze head, Cast Iron bearing housing	Bronze head, Cast Iron bearing housing
Impeller	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile	Neoprene or Nitrile
Wearplate	Replaceable	Replaceable	Replaceable	Replaceable	Replaceable
Shaft Material	Stainless Steel	Stainless Steel	Stainless Steel	Stainless Steel	Stainless Steel
Seal	Lip type	Carbon/ceramic mechanical type	Carbon/ceramic mechanical type	Carbon/ceramic mechanical type	Carbon/ceramic mechanical type
Bearings	Twin row, ball type	Twin single row, ball type	Twin single row, ball type	Twin single row, ball type	Twin single row, ball type
Port Type	1" BSP to BS21 (DIN2999)	1 1/2" BSP to BS21 (DIN2999)	1 1/2" Flange	2" Flange or BSP to BS21 (DIN2999)	1" BSP to BS21 (DIN2999)
Clutch Type	Manual - Self Adjusting	Manual - Self Adjusting	Manual - Self Adjusting	Manual - Self Adjusting	Manual - Self Adjusting
Pulley	180mm (7") 'A' or 'B' section	180mm (7") 'A' or 'B' section	180mm (7") 'A' or 'B' section	180mm (7") 'A' or 'B' section	180mm (7") 'A' or 'B' section
Weight (lb. / kg.)	5 / 11	8 / 17.6	10 / 22	11 / 24.2	6.3 / 13.8