

RULE LIVEWELL PUMP SERIES MODEL NUMBER TABLE

Model Number	Open Flow	Inlet Style	Inlet Size - NPT	Discharge Size - Hose Barb	Voltage	Amp Draw @ 12V DC	Fuse Size	Replacement Motor Cartridge PN
601FC	500 GPH	Straight seacock	3/4" NPT thread	3/4"	12 VDC	3.0 Amp	5 Amp	65DR
603FC	800 GPH	Straight seacock	3/4" NPT thread	3/4"	12 VDC	4.1 Amp	7.5 Amp	66DR
605FC	1100 GPH	Straight seacock	3/4" NPT thread	1 1/8"	12 VDC	4.7 Amp	7.5 Amp	67DR
601STC	500 GPH	Straight thru-hull	3/4" NPT thread	3/4"	12 VDC	3.0 Amp	5 Amp	65DR
603STC	800 GPH	Straight thru-hull	3/4" NPT thread	3/4"	12 VDC	4.1 Amp	7.5 Amp	66DR
605STC	1100 GPH	Straight thru-hull	3/4" NPT thread	1 1/8"	12 VDC	4.7 Amp	7.5 Amp	67DR
601C	500 GPH	Angled thru-hull	3/4" NPT thread	3/4"	12 VDC	3.0 Amp	5 Amp	65DR
603C	800 GPH	Angled thru-hull	3/4" NPT thread	3/4"	12 VDC	4.1 Amp	7.5 Amp	66DR
605C	1100 GPH	Angled thru-hull	3/4" NPT thread	1 1/8"	12 VDC	4.7 Amp	7.5 Amp	67DR