

RULE AUTOMATIC BILGE PUMPS

CAPACITY GPH (LPH)	MODEL NUMBER	VOLTS	FUSE SIZE	AMPS @12V	AMPS @13.6V	REPLACEMENT STRAINER	HEIGHT INCHES (mm)	WIDTH INCHES (mm)	HOSE DIAMETER INCHES (mm)	PANEL SWITCHES
500 (1893)	25SA	12DC	4	2.1	2.4	Model 1231R	4.2 (107)	2.9 (74)	3/4 (19)	41, 43, 45
500 (1893)	25SA-24	24DC	3	1@24V	1.2@24V	Model 1231R	4.2 (107)	2.9 (74)	3/4 (19)	41, 43, 46
800 (3028)	20SA	12DC	7.5	3.4	4.3	Model 1232R	4.7 (120)	2.9 (74)	3/4 (19)	41, 43, 45
1100 (4164)	27SA	12DC	7.5	3.7	4.7	Model 1232R	4.7 (120)	2.9 (74)	1-1/8 (29) / 1 (25)	41, 43, 45
1100 (4164)	27SA-24	24DC	4.0	1.9@24V	2.2@24V	Model 1232R	4.7 (120)	2.9 (74)	1-1/8 (29) / 1 (25)	41, 43, 46
1500 (5678)	51S	12DC	10	5	7.0	Model 286	7.75 (197)	4.75 (121)	1-1/8 (29)	41, 43, 45
2000 (7571)	53S	12DC	15.0	8.4	12	Model 278	7.75 (197)	4.75 (121)	1-1/8 (29)	41, 43, 45
3700 (14010)	55S	12DC	25	15.5	20	Model 279	8.25 (209)	4.9 (124)	1-1/2 (38)	41, 43, 45
4000 (15140)	56S	12DC	25	15.5	20	Model 279	9.25 (235)	4.9 (124)	2 (51)	41, 43, 45