

TOURNAMENT SERIES LIVEWELL-BAITWELL PUMPS

Model No.	Pump Type	Flow Rate	Voltage	Discharge
209B	bronze base	1600 GPH (6056 LPH)	12 Vdc	1-1/8 inch (28.6mm)
209FDP	dual port	1600 GPH (6056 LPH)	12 Vdc	1-1/8 inch (28.6mm)
401C	angled inlet	500 GPH (1893 LPH)	12 Vdc	1-1/8 inch (28.6mm)
403C	angled inlet	800 GPH (3028 LPH)	12 Vdc	1-1/8 inch (28.6mm)
405C	angled inlet	1000 GPH (3785 LPH)	12 Vdc	1-1/8 inch (28.6mm)
401FC	seacock inlet	500 GPH (1893 LPH)	12 Vdc	3/4 inch (19mm)
403FC	seacock inlet	800 GPH (3028 LPH)	12 Vdc	3/4 inch (19mm)
405FC	seacock inlet	1100 GPH (4164 LPH)	12 Vdc	1-1/8 inch (28.6mm)
401STC	straight inlet	500 GPH (1893 LPH)	12 Vdc	1-1/8 inch (28.6mm)
403STC	straight inlet	800 GPH (3028 LPH)	12 Vdc	3/4 inch (19mm)
405STC	straight inlet	1100 GPH (4164 LPH)	12 Vdc	1-1/8 inch (28.6mm)