



Tapped Full Circle® Repair Clamp

All Stainless Steel, Fabricated Lugs, Double Band

265

IMPORTANT LINKS

Click appropriate words
to go to:

[Standard Limited Warranty](#)

[Sales Terms & Conditions](#)

[Freight Policy](#)

[Returns Policy](#)

[Corrosion & Product Selection
Notice](#)



**THIS PRODUCT DOES NOT
RESTRAIN PIPE MOVEMENT.**
Proper anchoring is required to
prevent pipe pullout. Failure to
anchor or improper anchoring can
result in dangerous pipe content
escape, property damage, serious
injury, or death. Read the product
installation instructions prior to
installing this product.

Description: A double-band clamp designed to provide 360° pressure and complete leak repair

Application: For leaks at service outlets.

Key Features:

- Standard widths 7.5" through 30"
- Can be used to repair pipe or join pipe ends
- Can be manufactured to odd size pipe O.D.'s
- All 304 Stainless Steel construction for corrosion resistance
- A 360° Gasket seal provides maximum support and reinforcement
- A wide variety of outlet sizes and thread types available to meet demand
- Keeper bar helps pull clamp around the pipe and closes the clamp during installation
- Range up to .80"
- Larger clamps have a greater range to help reduce inventory

Materials Specifications (subject to change):

BAND: 304 Stainless Steel

LUGS: 304 Stainless Steel

KEEPER BARS: 304 Stainless Steel

GASKET: Nitrile (Buna N) to produce superior storage and performance characteristics while resisting water, acids, alkalies, most (aliphatic) hydrocarbon and other chemicals.

Temperature Range: -20°F to +180°F

BRIDGE PLATE: 304 Stainless Steel recessed flush and bonded to gasket

STUD BOLTS: 304 Stainless Steel Epoxy coated

NUTS: Fluoropolymer coated to prevent galling

Working Pressure: Up to 150 PSI

Pipe Applications: Cast Iron, Ductile Iron, Asbestos Cement, PVC, HDPE*, Steel, Copper, Fiberglass and other types of pipes.

*HDPE applications require clamps with spring washers.

Sizes (in inches): 4, 6, 8, 10, 12, ¾", 1" NPT and CC. 1¼", 1½", and 2" NPT. 2" CC

Bolt Numbers

BAND WIDTH INCHES	NUMBER OF STUDS	STUD SIZES
7.5	4	5/8" x 7"
10	6	
12.5	6	
15	8	



Tapped Full Circle® Repair Clamp

265

All Stainless Steel, Fabricated Lugs, Double Band

¾" and 1" NPT and CC Taps

STANDARD				¾" NPT 20 MM	¾" CC 20 MM	1" NPT 25 MM	1" CC 25 MM	METRIC			
NOM. SIZE INCH.	O.D. RANGE INCHES	WIDTH INCH.	WT. EACH LBS.	CATALOG NUMBER	CATALOG NUMBER	CATALOG NUMBER	CATALOG NUMBER	NOM. SIZE MM	O.D. RANGE MM	WIDTH MM	WT. EACH KG.
4	4.44-5.24	7.5	11	265-045007-006	265-045007-007	265-045007-008	265-045007-009	100	113-133	190	4.5
		10	13	265-045010-006	265-045010-007	265-045010-008	265-045010-009			254	5.9
		12.5	16	265-045012-006	265-045012-007	265-045012-008	265-045012-009			317	7.3
		15	19	265-045015-006	265-045015-007	265-045015-008	265-045015-009			381	8.6
6	6.62-7.42	7.5	12	265-066307-006	265-066307-007	265-066307-008	265-066307-009	150	168-189	190	5.4
		10	16	265-066310-006	265-066310-007	265-066310-008	265-066310-009			254	7.3
		12.5	19	265-066312-006	265-066312-007	265-066312-008	265-066312-009			317	8.6
		15	23	265-066315-006	265-066315-007	265-066315-008	265-066315-009			381	10.4
6	6.84-7.64	7.5	12	265-069007-006	265-069007-007	265-069007-008	265-069007-009	150	174-194	190	5.4
		10	16	265-069010-006	265-069010-007	265-069010-008	265-069010-009			254	7.3
		12.5	19	265-069012-006	265-069012-007	265-069012-008	265-069012-009			317	8.6
		15	23	265-069015-006	265-069015-007	265-069015-008	265-069015-009			381	10.4
8	8.62-9.42	7.5	13	265-086307-006	265-086307-007	265-086307-008	265-086307-009	200	219-239	190	5.9
		10	17	265-086310-006	265-086310-007	265-086310-008	265-086310-009			254	7.7
		12.5	21	265-086312-006	265-086312-007	265-086312-008	265-086312-009			317	9.5
		15	25	265-086315-006	265-086315-007	265-086315-008	265-086315-009			381	11.3
8	8.99-9.79	7.5	17	265-090507-006	265-090507-007	265-090507-008	265-090507-009	200	229-248	190	7.7
		10	21	265-090510-006	265-090510-007	265-090510-008	265-090510-009			254	9.5
		12.5	25	265-090512-006	265-090512-007	265-090512-008	265-090512-009			317	11.3
		15	26	265-090515-006	265-090515-007	265-090515-008	265-090515-009			381	11.8
10	10.75-11.55	10	23	265-107510-006	265-107510-007	265-107510-008	265-107510-009	250	273-293	254	10.4
		12.5	27	265-107512-006	265-107512-007	265-107512-008	265-107512-009			317	12.2
		15	33	265-107515-006	265-107515-007	265-107515-008	265-107515-009			381	15.0
10	11.10-11.90	10	23	265-111010-006	265-111010-007	265-111010-008	265-111010-009	250	282-302	254	10.4
		12.5	28	265-111012-006	265-111012-007	265-111012-008	265-111012-009			317	12.7
		15	34	265-111015-006	265-111015-007	265-111015-008	265-111015-009			381	15.4
12	12.75-13.55	10	25	265-127510-006	265-127510-007	265-127510-008	265-127510-009	300	324-344	254	11.3
		12.5	29	265-127512-006	265-127512-007	265-127512-008	265-127512-009			317	13.2
		15	37	265-127515-006	265-127515-007	265-127515-008	265-127515-009			381	16.8
12	13.20-14.00	10	25	265-132010-006	265-132010-007	265-132010-008	265-132010-009	300	335-355	254	11.3
		12.5	29	265-132012-006	265-132012-007	265-132012-008	265-132012-009			317	13.2
		15	37	265-132015-006	265-132015-007	265-132015-008	265-132015-009			381	17.7

NOTE: Additional widths, OD ranges and tap sizes available upon request.

1¼", 1½" and 2" NPT Taps, and 2" CC Taps

STANDARD				1 1/4" NPT 32 MM	1 1/2" NPT 38 MM	2" NPT 50 MM	2" CC 50 MM	METRIC			
NOM. SIZE INCH.	O.D. RANGE INCHES	WIDTH INCH.	WT. EACH LBS.	CATALOG NUMBER	CATALOG NUMBER	CATALOG NUMBER	CATALOG NUMBER	NOM. SIZE MM	O.D. RANGE MM	WIDTH MM	WT. EACH KG.
4	4.44-5.24	7.5	10	265-045007-010	265-045007-012	265-045007-014	265-045007-015	100	113-133	190	4.5
		10	13	265-045010-010	265-045010-012	265-045010-014	265-045010-015			254	5.9
		12.5	16	265-045012-010	265-045012-012	265-045012-014	265-045012-015			317	7.3
		15	19	265-045015-010	265-045015-012	265-045015-014	265-045015-015			381	8.6
6	6.62-7.42	7.5	12	265-066307-010	265-066307-012	265-066307-014	265-066307-015	150	168-189	190	5.4
		10	16	265-066310-010	265-066310-012	265-066310-014	265-066310-015			254	7.3
		12.5	19	265-066312-010	265-066312-012	265-066312-014	265-066312-015			317	8.6
		15	23	265-066315-010	265-066315-012	265-066315-014	265-066315-015			381	10.4
6	6.84-7.64	7.5	12	265-069007-010	265-069007-012	265-069007-014	265-069007-015	150	174-194	190	5.4
		10	16	265-069010-010	265-069010-012	265-069010-014	265-069010-015			254	7.3
		12.5	19	265-069012-010	265-069012-012	265-069012-014	265-069012-015			317	8.6
		15	23	265-069015-010	265-069015-012	265-069015-014	265-069015-015			381	10.4
8	8.62-9.42	7.5	13	265-086307-010	265-086307-012	265-086307-014	265-086307-015	200	219-239	190	5.9
		10	17	265-086310-010	265-086310-012	265-086310-014	265-086310-015			254	7.7
		12.5	21	265-086312-010	265-086312-012	265-086312-014	265-086312-015			317	9.5
		15	25	265-086315-010	265-086315-012	265-086315-014	265-086315-015			381	11.3
8	8.99-9.79	7.5	17	265-090507-010	265-090507-012	265-090507-014	265-090507-015	200	229-248	190	7.7
		10	21	265-090510-010	265-090510-012	265-090510-014	265-090510-015			254	9.5
		12.5	25	265-090512-010	265-090512-012	265-090512-014	265-090512-015			317	11.3
		15	26	265-090515-010	265-090515-012	265-090515-014	265-090515-015			381	11.8
10	10.75-11.55	10	23	265-107510-010	265-107510-012	265-107510-014	265-107510-015	250	273-293	254	10.4
		12.5	27	265-107512-010	265-107512-012	265-107512-014	265-107512-015			317	12.2
		15	33	265-107515-010	265-107515-012	265-107515-014	265-107515-015			381	15.0
10	11.10-11.90	10	23	265-111010-010	265-111010-012	265-111010-014	265-111010-015	250	282-302	254	10.4
		12.5	28	265-111012-010	265-111012-012	265-111012-014	265-111012-015			317	12.7
		15	34	265-111015-010	265-111015-012	265-111015-014	265-111015-015			381	15.4
12	12.75-13.55	10	25	265-127510-010	265-127510-012	265-127510-014	265-127510-015	300	324-344	254	11.3
		12.5	29	265-127512-010	265-127512-012	265-127512-014	265-127512-015			317	13.2
		15	37	265-127515-010	265-127515-012	265-127515-014	265-127515-015			381	16.8
12	13.20-14.00	10	25	265-132010-010	265-132010-012	265-132010-014	265-132010-015	300	335-355	254	11.3
		12.5	29	265-132012-010	265-132012-012	265-132012-014	265-132012-015			317	13.2
		15	37	265-132015-010	265-132015-012	265-132015-014	265-132015-015			381	17.7

NOTE: Additional widths, OD ranges and tap sizes available upon request.