



# Bronze Service Saddle

## Extra Wide Stainless Strap

# 325

### IMPORTANT LINKS

Click appropriate words to go to:

[Standard Limited Warranty](#)  
[Sales Terms & Conditions](#)  
[Freight Policy](#)  
[Returns Policy](#)  
[Corrosion & Product Selection Notice](#)



**Description:** Bronze Service Saddle with Stainless Steel strap

**Application:** Ideal for PVC pipe and will provide added corrosion resistance.

#### Key Features:

- Buna-N Gasket per ASTM D2000
- Meets applicable AWWA C800 Standards
- Available with 3/4" thru 2" NPT and CC outlets
- Body made of Cast Red Brass for corrosion resistance
- Designed with PVC Pipe applications in mind. O.D. Specific bodies are available
- Maximum support and reinforcement on PVC pipe (nearly 360°)
- Strap will provide a range that covers Steel and Ductile Iron O.D.'s on rigid pipe
- Strap is single 3.5" wide, 304 Stainless Steel, four studs for wide stance on the pipe

#### Materials Specifications (subject to change):

BODY: 85-5-5-5 Cast Red Brass per ASTM B584 or B62

GASKET: NSF-61 Approved Buna-N

Temperature Range: -20°F to 180°F

STRAPS: 18-8 Type 304 Stainless Steel

NUTS/WASHERS: 18-8 Type 304 Premium Grade Stainless Nuts, coated to prevent galling

**Working Pressure:** 150 PSI, depending on size and application

**Pipe Applications:** PVC, Ductile Iron, Cast Iron and Steel

**Sizes (in inches):** 4, 6, 8, 10, 12



# Bronze Service Saddle

## Extra Wide Stainless Strap

325

3/4" and 1" NPT and CC Taps

For Rigid Pipe Applications

NOM. SIZE IN.	O.D. RANGE INCHES	CTN. QTY.	CATALOG NUMBER				WT. EACH LBS.
			3/4" NPT	3/4" CC	1" NPT	1" CC	
4	4.50 - 4.80	4	325-048006-100	325-048007-100	325-048008-100	325-048009-100	6.3
6	6.63 - 6.90	4	325-069006-100	325-069007-100	325-069008-100	325-069009-100	7.3
8	8.63 - 9.05	4	325-090506-100	325-090507-100	325-090508-100	325-090509-100	7.9
10	10.75 - 11.10	4	325-111006-100	325-111007-100	325-111008-100	325-111009-100	9.3
12	12.75 - 13.20	2	325-132006-100	325-132007-100	325-132008-100	325-132009-100	10.3

3/4" and 1" NPT and CC Taps

For PVC Pipe Applications

NOM. SIZE IN.	O.D. INCHES	CTN. QTY.	CATALOG NUMBER				WT. EACH LBS.
			3/4" NPT	3/4" CC	1" NPT	1" CC	
4	4.50	4	325-045006-000	325-045007-000	325-045008-000	325-045009-000	6.3
	4.80	4	325-048006-000	325-048007-000	325-048008-000	325-048009-000	6.3
6	6.63	4	325-066306-000	325-066307-000	325-066308-000	325-066309-000	7.3
	6.90	4	325-069006-000	325-069007-000	325-069008-000	325-069009-000	7.3
8	8.63	4	325-086306-000	325-086307-000	325-086308-000	325-086309-000	7.9
	9.05	4	325-090506-000	325-090507-000	325-090508-000	325-090509-000	7.9
10	10.75	4	325-107506-000	325-107507-000	325-107508-000	325-107509-000	9.3
	11.10	4	325-111006-000	325-111007-000	325-111008-000	325-111009-000	9.3
12	12.75	2	325-127506-000	325-127507-000	325-127508-000	325-127509-000	10.3
	13.20	2	325-132006-000	325-132007-000	325-132008-000	325-132009-000	10.3

1 1/4" - 2" NPT and CC Taps

For PVC Pipe Applications

NOM. SIZE IN.	O.D. INCH.	CTN. QTY.	CATALOG NUMBER						WT. EACH LBS.
			1 1/4" NPT	1 1/4" CC	1 1/2" NPT	1 1/2" CC	2" NPT	2" CC	
4	4.50	4	325-045010-000	325-045011-000	325-045012-000	325-045013-000	325-045014-000	325-045015-000	7.5
	4.80	4	325-048010-000	325-048011-000	325-048012-000	325-048013-000	325-048014-000	325-048015-000	7.5
6	6.63	4	325-066310-000	325-066311-000	325-066312-000	325-066313-000	325-066314-000	325-066315-000	7.9
	6.90	4	325-069010-000	325-069011-000	325-069012-000	325-069013-000	325-069014-000	325-069015-000	7.9
8	8.63	4	325-086310-000	325-086311-000	325-086312-000	325-086313-000	325-086314-000	325-086315-000	9.1
	9.05	4	325-090510-000	325-090511-000	325-090512-000	325-090513-000	325-090514-000	325-090515-000	9.1
10	10.75	4	325-107510-000	325-107511-000	325-107512-000	325-107513-000	325-107514-000	325-107515-000	10.3
	11.10	4	325-111010-000	325-111011-000	325-111012-000	325-111013-000	325-111014-000	325-111015-000	10.3
12	12.75	2	325-127510-000	325-127511-000	325-127512-000	325-127513-000	325-127514-000	325-127515-000	11.5
	13.20	2	325-132010-000	325-132011-000	325-132012-000	325-132013-000	325-132014-000	325-132015-000	11.5

When properly sized from the factory, this product (denoted by \*) meets the requirements listed in the Uni-Bell PVC Pipe Association's "Handbook of PVC Pipe" and in the AWWA's "Manual M23: PVC Pipe Design and Installation."

## 1 1/4" – 2" NPT and CC Taps SS Straps

NOM. SIZE IN.	O.D. RANGE INCHES	CTN. QTY.	CATALOG NUMBER						WT. EACH LBS.
			1 1/4" NPT	1 1/4" CC	1 1/2" NPT	1 1/2" CC	2" NPT	2" CC	
4	4.50 - 4.80	4	325-048010-100	325-048011-100	325-048012-100	325-048013-100	325-048014-100	325-048015-100	7.5
6	6.63 - 6.90	4	325-069010-100	325-069011-100	325-069012-100	325-069013-100	325-069014-100	325-069015-100	7.9
8	8.63 - 9.05	4	325-090510-100	325-090511-100	325-090512-100	325-090513-100	325-090514-100	325-090515-100	9.1
10	10.75 - 11.10	4	325-111010-100	325-111011-100	325-111012-100	325-111013-100	325-111014-100	325-111015-100	10.3
12	12.75 - 13.20	2	325-132010-100	325-132011-100	325-132012-100	325-132013-100	325-132014-100	325-132015-100	11.5

When properly sized from the factory, this product (denoted by \*) meets the requirements listed in the Uni-Bell PVC Pipe Association's "Handbook of PVC Pipe" and in the AWWA's "Manual M23: PVC Pipe Design and Installation."