



Tapping Sleeve

MJ Outlet available on any style tapping sleeve

MJ

IMPORTANT LINKS

Click appropriate words to go to:

[Standard Limited Warranty](#)

[Sales Terms & Conditions](#)

[Freight Policy](#)

[Returns Policy](#)

[Corrosion & Product Selection Notice](#)

Description: MJ outlet is available on any style of tapping sleeve.

Application: Taps utilizing standard MJ valve.

Key Features:

- The MJ Outlet allows the user to tap pipe, utilizing a standard MJ x MJ valve in lieu of a specialty tapping valve
- This outlet allows the user to combine valve inventory to a single valve, reduce installation time and save money
- The heavy mechanical joint flange is fixed in place to make installation easier, while reducing the chance of injuries during the tapping operation

Materials Specifications (subject to change):

FLANGES: Drilling per ANSI/AWWA C111/A21.11. Fusion-Bonded, Flexi-Coat® epoxy coated Carbon Steel on 622/662/664. 18-8 type 304 Stainless Steel flange on 663/665

Working Pressure: Up to fitting design.

Pipe Applications: Steel, Cast Iron, Asbestos Cement, PVC

Sizes (in inches): Call Smith-Blair for more information on sizes and pricing.