



FLANGED COUPLING ADAPTERS



921 TOP BOLT FLANGED COUPLING ADAPTERS

Nominal Size (IN.)	Catalog Number	Overall Range (IN.)	Lower Range (IN.)	Upper Range (IN.)	Width (IN.)	Height (IN.)	Flange Diameter (IN.)	Laying Length (IN.)	Approx. Weight lbs.	List Price
2	921-02950200-031	2.13 - 2.95	2.13 - 2.60	2.50 - 2.95	5.38	7.25	6.00	6.81	8	\$224.39
3	921-04200300-031	3.10-4.20	3.10-3.56	3.70-4.20	6.88	8.38	7.50	5.38	12	318.99
4	921-05600400-031	4.46-5.60	4.46-5.05	5.00-5.60	8.75	10.00	9.00	5.50	17	411.87
6	921-07600600-031	6.56-7.60	6.56-7.05	7.00-7.60	10.88	12.13	11.00	6.56	25	521.27
8	921-09850800-031	8.54-9.85	8.54-9.15	9.15-9.85	13.13	14.38	13.50	6.56	30	710.64
10	921-11831000-031	10.64-11.83	10.64-11.18	11.13-11.83	15.50	16.50	16.00	6.56	37	1,205.03
12	921-13671200-031	12.62-13.67	12.62-13.06	13.10-13.67	17.63	18.75	19.00	6.69	50	1,389.99

922 TOP BOLT FLANGED COUPLING ADAPTERS- EXTENDED SLEEVE LENGTH

Nominal Size (IN.)	Catalog Number	Overall Range (IN.)	Lower Range (IN.)	Upper Range (IN.)	Width (IN.)	Height (IN.)	Flange Diameter (IN.)	Laying Length (IN.)	Approx. Weight lbs.	List Price
2	922-02950200-031	2.13 - 2.95	2.13 - 2.60	2.50 - 2.95	5.38	7.25	6.00	9.00	12	\$269.30
3	922-04200300-031	3.10-4.20	3.10-3.56	3.70-4.20	6.88	8.38	7.50	9.00	18	382.80
4	922-05600400-031	4.46-5.60	4.46-5.05	5.00-5.60	8.75	10.00	9.00	9.00	26	494.25
6	922-07600600-031	6.56-7.60	6.56-7.05	7.00-7.60	10.88	12.13	11.00	12.00	35	625.50
8	922-09850800-031	8.54-9.85	8.54-9.15	9.15-9.85	13.13	14.38	13.50	12.00	45	852.80
10	922-11831000-031	10.64-11.83	10.64-11.18	11.13-11.83	15.50	16.50	16.00	12.00	56	1,446.00
12	922-13671200-031	12.62-13.67	12.62-13.06	13.10-13.67	17.63	18.75	19.00	12.00	75	1,668.00