



0

straight pipe requirements enable installation anywhere



0.05

GPM starting flow detection (2-inch)



3

measurement channels to provide superior accuracy



20

20 years of non-prorated accuracy warranty + 15-year full replacement/5-year prorated on batteries and components



180

days of hourly consumption, temperature, and pressure data logging



1,000

turndown ratio = accuracy at extreme lows and highs

