

3887 2WFH

PUMP TO PANELS PART NUMBERS

Pump	HP	Phase	Voltage	Amps	Simplex Panel	Duplex Panel
2WF0311H	0.33	1	115	12.4	C4S10020	C4D10020
2WF0318H	0.33	1	208	6.8	C4S10020	C4D10020
2WF0312H	0.33	1	230	6.2	C4S10020	C4D10020
2WF0511H	0.5	1	115	14.5	C4S10020	C4D10020
2WF0518H	0.5	1	208	8.4	C4S10020	C4D10020
2WF0512H	0.5	1	230	7.6	C4S10020	C4D10020
2WF0538H	0.5	3	200	4.9	C4S34063	C4D34063
2WF0532H	0.5	3	230	3.6	C4S32540	C4D32540
2WF0534H	0.5	3	460	1.8	C4S31625	C4D31625
2WF0537H	0.5	3	575	1.5	C4S31625	C4D31625
2WF0718H	0.75	1	208	11	C4S10020	C4D10020
2WF0712H	0.75	1	230	10	C4S10020	C4D10020
2WF0738H	0.75	3	200	6.2	C4S34063	C4D34063
2WF0732H	0.75	3	230	5.4	C4S34063	C4D34063
2WF0734H	0.75	3	460	2.7	C4S32540	C4D32540
2WF0737H	0.75	3	575	2.2	C4S31625	C4D31625
2WF1018H	1	1	208	14.5	C4S10020	C4D10020
2WF1012H	1	1	230	13	C4S10020	C4D10020
2WF1038H	1	3	200	8.6	C4S36310	C4D36310
2WF1032H	1	3	230	7.5	C4S36310	C4D36310
2WF1034H	1	3	460	3.8	C4S32540	C4D32540
2WF1037H	1	3	575	3.1	C4S32540	C4D32540
2WF1512H	1.5	1	230	18	C4S10020	C4D10020
2WF1538H	1.5	3	200	10	C4S31016	C4D31016
2WF1532H	1.5	3	230	9.6	C4S36310	C4D36310
2WF1534H	1.5	3	460	4.8	C4S34063	C4D34063
2WF1537H	1.5	3	575	3.9	C4S32540	C4D32540
2WF2012H	2	1	230	18	C4S10020	C4D10020
2WF2038H	2	3	200	12	C4S31016	C4D31016
2WF2032H	2	3	230	11.6	C4S31016	C4D31016
2WF2034H	2	3	460	5.8	C4S34063	C4D34063
2WF2037H	2	3	575	4.7	C4S34063	C4D34063