

38884WDA

PUMP TO PANEL PART NUMBERS

Pump	HP	Phase	Voltage	Amps	Simplex Panel	Duplex Panel
4WDA1518M	1.5	1	208	17.2	C4S10020	C4D10020
4WDA1512M	1.5	1	230	14.7	C4S10020	C4D10020
4WDA1538M	1.5	3	200	11.5	C4S31016	C4D31016
4WDA1532M	1.5	3	230	10	C4S31016	C4D31016
4WDA1534M	1.5	3	460	5	C4S34063	C4D34063
4WDA1537M	1.5	3	575	4	C4S34063	C4D34063
4WDA1518	1.5	1	208	17.2	C4S10020	C4D10020
4WDA1512	1.5	1	230	14.7	C4S10020	C4D10020
4WDA1538	1.5	3	200	11.5	C4S31016	C4D31016
4WDA1532	1.5	3	230	10	C4S31016	C4D31016
4WDA1534	1.5	3	460	5	C4S34063	C4D34063
4WDA1537	1.5	3	575	4	C4S34063	C4D34063
4WDA2018	2	1	208	20.3	C4S12136	C4D12136
4WDA2012	2	1	230	17.3	C4S10020	C4D10020
4WDA2038	2	3	200	13.3	C4S31016	C4D31016
4WDA2032	2	3	230	11.6	C4S31016	C4D31016
4WDA2034	2	3	460	5.8	C4S34063	C4D34063
4WDA2037	2	3	575	4.6	C4S34063	C4D34063
4WDA3018	3	1	208	25.5	C4S12136	C4D12136
4WDA3012	3	1	230	21.5	C4S12136	C4D12136
4WDA3038	3	3	200	16.6	C4S31620	C4D31620
4WDA3032	3	3	230	14.4	C4S31016	C4D31016
4WDA3034	3	3	460	7.2	C4S36310	C4D36310
4WDA3037	3	3	575	5.8	C4S34063	C4D34063
4WDA5012	5	1	230	26.5	C4S12136	C4D12136
4WDA5038	5	3	200	19.1	C4S31620	C4D31620
4WDA5032	5	3	230	16.6	C4S31620	C4D31620
4WDA5034	5	3	460	8.3	C4S36310	C4D36310
4WDA5037	5	3	575	6.6	C4S36310	C4D36310
4WDA7532	7.5	3	230	23	C4S32025	C4D32025
4WDA7534	7.5	3	460	11.5	C4S31016	C4D31016
4WDA7537	7.5	3	575	9.2	C4S36310	C4D36310