



PH-10 Handheld pH Meter



- Advanced technology
- Handy pocket size
- Automatic calibration
- Waterproof housing
- Replaceable epoxy body, gel filled pH sensor

Description

The Pinnacle Chek-Mite Handheld pH Meters provide a whole new level of performance in an inexpensive line of handheld metering instrumentation. Featuring advanced microprocessor technology, the pH meters offer automatic calibration (to values of 4, 7, or 10.01) and options such as automatic temperature compensation (ATC), automatic endpoint, and BNC connection. Sealed components and casing are waterproof, and enable the meters to float when dropped in water. The pH-10, pH-15 and pH-20 Handheld pH Meters offer replaceable electrode sensors. This line of pH meters comes with a six-month warranty.

Chek-Mite pH-10

This Handheld pH Meter offers value and performance for pH measurement. This meter automatically recognizes buffer solutions 4, 7, and 10.01, and then calibrates on that value, there are no manual adjustments to make.

Chek-Mite pH-15

This Handheld pH Meter measures pH based on an automatic calibration. The Chek-Mite pH-15 Handheld pH Meter has a Manual endpoint which also provides the capability to freeze the display once a reading has stabilized.

Chek-Mite pH-20

Similar to the Chek-Mite pH-15, this meter offers the added convenience of automatic temperature compensation (ATC) and has an automatic endpoint adjustment.

Specifications

Specification	pH-10	pH-15	pH-20
Range:	0-14	0-14	0-14
Resolution:	0.01	0.01	0.01
Accuracy:	±0.2 pH	±0.04 pH	±0.04 pH
Temperature Compensation:	Set @ 77 F (25 C)	Set @ 77 F (25 C)	Automatic from 0-122 F (0-50 C)
Calibration:	Auto	Auto	Auto
# of Calibration Points:	2 of 3	2 of 3	2 of 3
ISO Potential Point:	7 pH	7 pH	7 pH
Sensor Type:	Combo	Combo	3 in 1
Replaceable:	Yes	Yes	Yes

Options and Accessories

pH-10 Handheld pH Meter

pH-15 Handheld pH Meter

pH-20 Handheld pH Meter

473040 pH electrode for pH-10

473051 pH electrode for pH-15

473049 pH electrode for pH-20



Global Water
a xylem brand

In the U.S. call toll free
at 1-800-876-1172
International: 1-979-690-5560
Fax: 1-979-690-0440
Email: globalw@globalw.com

Visit our online catalog at:
www.globalw.com
Our Address:
11390 Amalgam Way
Gold River, CA 95670