

# Insta-Test® Test Strips

Fast Water Quality Testing Strips



## Description

The popular Insta-Test Test Strips are essential for examining water quality. They provide quick and easy water quality profiles for drinking water, food and beverage, and pool applications.

## Specifications\*

### Single Factor Test Strips

Order No.	Test Factor	Range (ppm)	Water Testing Application	# of Tests Per Factor/Vial	Values (ppm)
2997	Alkalinity	0-180	Drinking, Food/Beverage, Pool	50	0, 40, 80, 120, 180
2964-G	Chlorine, Free, Low Range	0-10	Drinking, Food/Beverage, Pool	25	0, 0.25, 0.5, 1, 3, 5, 10
2963LR-G	Chlorine, Total, Low Range	0-10	Drinking, Food/Beverage	25	0, 0.1, 0.25, 0.5, 1, 3, 10
2979	Chlorine, Total	0-5	Drinking, Food/Beverage	50	0, 0.5, 1, 3, 5
2981	Hardness, Low Range	0-180	Drinking, Food/Beverage	50	0, 30, 60, 120, 180
2974	pH, Wide Range	4-10 (pH)	Drinking, Food/Beverage, Pool	50	4, 5, 6, 7, 8, 9, 10
2984	Peroxide	0-100	Drinking, Food/Beverage	25	0, 1, 3, 10, 30, 100

### Multi-Factor Test Strips


Order No.	Test Factor	Range (ppm)	Water Testing Application	# of Tests Per Factor/Vial	Values (ppm)
2980	Iron, pH & Hardness	0-5 (Iron)	Drinking	25	0, 0.3, 0.5, 1, 3, 5
		4-10 (pH)		25	4, 5, 6, 7, 8, 9, 10
		0-400 (Hard)		25	0, 50, 100, 200, 400
2987	Wide Range (pH & Total Chlorine)	4-10 (pH)	Drinking, Food/Beverage, Pool	50	4, 5, 6, 7, 8, 9, 10
		0-50 (TCI)		50	0, 1, 5, 10, 20, 50
2996	Nitrate & Nitrite	0-50 (Nitrate)	Drinking	50	0, 5, 10, 25, 50 (NO <sub>3</sub> -N)
		0-10 (Nitrite)		50	0, 0.5, 1, 5, 10 (NO <sub>2</sub> -N)

\* Strips have been evaluated for use in the specified applications. Use in other applications is subject to potential interferences.

## Features

- Quick and easy
- Examine a variety of parameters
- Available for single and multiple factor testing

## Applications



Ideal for drinking water treatment, the food and beverage industry, and pool testing.

## Ordering & Options

### Single Factor Test Strips

Order No.	Test Factor
2997	Alkalinity
2964-G	Chlorine, Free, Low Range
2963LR-G	Chlorine, Total, Low Range
2979	Chlorine, Total
2981	Hardness, Low Range
2974	pH, Wide Range
2984	Peroxide

### Multi-Factor Test Strips

Order No.	Factors
2980	Iron, pH & Hardness
2987	Wide Range (pH & Total Chlorine)
2996	Nitrate & Nitrite



In the U.S. call toll free  
at 1-800-876-1172  
International: 1-979-690-5560  
Fax: 1-979-690-0440  
Email: [globalw@globalw.com](mailto:globalw@globalw.com)

Visit our online catalog at:  
[www.globalw.com](http://www.globalw.com)  
Our Address:  
11390 Amalgam Way  
Gold River, CA 95670