



RED JACKET SERIES

Enduro

60 HZ, ½ -5 HP, 4" SUBMERSIBLE PUMPS



Engineered, Assembled,
and Tested in the USA.
You can depend on the quality and
craftsmanship behind the Red Jacket Enduro.

FEATURES AND BENEFITS

- Utilizes an internal spring-loaded check valve design, optional external check valve available.
- Pump casing and cable guard constructed of heavy gauge 300-series corrosion resistant stainless steel for durability in aggressive conditions
- Floating Stage hydraulic design minimizes internal leakage resulting in increased pump efficiency
- Stainless steel discharge head and motor adapter for maximum strength and corrosion resistance.
- Powered by CentriPro motors featuring built-in lightning and thermal overload protection, a Kingsbury thrust bearing rated up to 1500 lbs, Copper Class F windings, and stainless construction
- Discharge head, casing and motor adapter have left-hand threads



 **GOULDS**
WATER TECHNOLOGY
a xylem brand

WATER END LENGTHS AND WEIGHTS

Order Number	Required HP	Stages	Length (in.)	Weight (lbs.)
6S17	½	17	22.1	13
6S21	¾	21	26.7	14
6S25	1	25	30.3	17
6S32	1½	32	36.6	20
8S12	½	12	17.2	11
8S16	¾	16	20.8	12
8S21	1	21	26.0	14
8S25	1½	25	29.6	17
8S30	2	30	34.0	21
8S43	3	43	46.4	34
12S8	½	8	13.8	9
12S9	½	9	14.7	10
12S12	¾	12	17.5	11
12S14	1	14	19.3	12
12S18	1½	18	23.7	13
12S23	2	23	28.3	17
12S32	3	32	36.6	22


Order Number	Required HP	Stages	Length (in.)	Weight (lbs.)
20S5	½	5	11.0	8
20S6	¾	6	12.0	8
20S8	1	8	13.8	8
20S11	1½	11	16.6	9
20S14	2	14	19.3	13
20S19	3	19	24.6	15
20S30	5	30	34.7	25
25S7	1	7	14.2	8
25S10	1½	10	17.6	9
25S12	2	12	19.8	10
25S17	3	17	26.0	15
25S28	5	28	38.3	23

SPECIFICATIONS

Model	Flow Range GPM	HP Range	Best Eff. GPM	Discharge Connection	Min. Well Size	Rotation ^①
6S	1.2 - 8.5	½ - 1½	5	1¼"	4 "	CCW
8S	1.5 - 10	½ - 3	7	1¼"	4 "	CCW
12S	3 - 13	½ - 3	10	1¼"	4 "	CCW
20S	6 - 25	½ - 5	18	1¼"	4 "	CCW
25S	8 - 31	1 - 5	22	1¼"	4 "	CCW

① Rotation is counterclockwise when viewed from pump discharge end

PERFORMANCE AREA CURVE



Xylem Inc.
 2881 East Bayard Street Ext., Seneca Falls, NY 13148
 Phone: (866) 325-4210 • Fax: (888) 322-5877
goulds.com/red-jacket

Goulds is a registered trademark of Goulds Pumps, Inc. and is used under license.
 Red Jacket Series is a trademark of Xylem Inc. or one of its subsidiaries.
 © 2021 Xylem Inc. ENDUROSALLES February 2021