

3888D4

PUMP-TO-PANEL PART NUMBERS

Pump	HP	Phase	Voltage	Amps	Simplex Panel	Duplex Panel
WS1518D4M	1.5	1	208	17.2	C4S10020	C4D10020
WS1512D4M	1.5	1	230	14.7	C4S10020	C4D10020
WS1538D4M	1.5	3	200	11.5	C4S31016	C4D31016
WS1532D4M	1.5	3	230	10	C4S31016	C4D31016
WS1534D4M	1.5	3	460	5	C4S34063	C4D34063
WS1537D4M	1.5	3	575	4	C4S34063	C4D34063
WS1518D4	1.5	1	208	17.2	C4S10020	C4D10020
WS1512D4	1.5	1	230	14.7	C4S10020	C4D10020
WS1538D4	1.5	3	200	11.5	C4S31016	C4D31016
WS1532D4	1.5	3	230	10	C4S31016	C4D31016
WS1534D4	1.5	3	460	5	C4S34063	C4D34063
WS1537D4	1.5	3	575	4	C4S34063	C4D34063
WS2018D4	2	1	208	20.3	C4S12136	C4D12127
WS2012D4	2	1	230	17.3	C4S10020	C4D10020
WS2038D4	2	3	200	13.3	C4S31016	C4D31016
WS2032D4	2	3	230	11.6	C4S31016	C4D31016
WS2034D4	2	3	460	5.8	C4S34063	C4D34063
WS2037D4	2	3	575	4.6	C4S34063	C4D34063
WS3018D4	3	1	208	25.5	C4S12136	C4D12836
WS3012D4	3	1	230	21.5	C4S12136	C4D12127
WS3038D4	3	3	200	16.6	C4S31620	C4D31620
WS3032D4	3	3	230	14.4	C4S31016	C4D31016
WS3034D4	3	3	460	7.2	C4S36310	C4D36310
WS3037D4	3	3	575	5.8	C4S34063	C4D34063
WS5012D4	5	1	230	26.5	C4S12136	C4D12836
WS5038D4	5	3	200	19.1	C4S31620	C4D31620
WS5032D4	5	3	230	16.6	C4S31620	C4D31620
WS5034D4	5	3	460	8.3	C4S36310	C4D36310
WS5037D4	5	3	575	6.6	C4S36310	C4D36310
WS7532D4	7.5	3	230	23	C4S32025	C4D32025
WS7534D4	7.5	3	460	11.5	C4S31016	C4D31016
WS7537D4	7.5	3	575	9.2	C4S36310	C4D36310