

4NS

PUMP-TO-PANEL PART NUMBERS

Order Number	HP	Volts	S.F. Amps	Simplex 3 Phase Panel Part Number	Duplex 3 Phase Panel Part Number
4NS12K3MC	7.5	230	23.4	NSS32432	NSD32432
4NS12K4MC		460	11.7	NSS39014	NSD39014
4NS12K5MC		575	9.4	NSS390145	NSD390145
4NS12L2KC	10	200	35.6	NSS33040	NSD33040
4NS12L3KC		230	31	NSS33040	NSD33040
4NS12L4KC		460	15.5	NSS31318	NSD31318
4NS12L5KC		575	12.3	NSS390145	NSD390145
4NS12M2GC	15	200	54.8	NSS34865	NSD34865
4NS12M3GC		230	47.8	NSS34865	NSD34865
4NS12M4GC		460	23.9	NSS32432	NSD32432
4NS12M5GC		575	19.1	NSS317235	NSD317235
4NS12N2EC	20	200	74.8	NSS365115	NSD365115
4NS12N3EC		230	65	NSS365115	NSD365115
4NS12N4EC		460	32.5	NSS33040	NSD33040
4NS12N5EC		575	26.0	NSS324325	NSD324325
4NS12P2CC	25	200	83.6	NSS365115	NSD365115
4NS12P3CC		230	72.8	NSS365115	NSD365115
4NS12P4CC		460	36.4	NSS33040	NSD33040
4NS12P5CC		575	29.1	NSS324325	NSD324325
4NS12Q2BC	30	200	103.2	NSS365115	NSD365115
4NS12Q3BC		230	89.6	NSS365115	NSD365115
4NS12Q4BC		460	44.8	NSS33750	NSD33750
4NS12Q5BC		575	35.8	NSS330405	NSD330405
4NS12R2AC	40	200	132.8	Consult factory for custom quote.	Consult factory for custom quote.
4NS12R3AC		230	115.4	Consult factory for custom quote.	Consult factory for custom quote.
4NS12R4AC		460	57.7	NSS34865	NSD34865
4NS12R5AC		575	46.2	NSS337505	NSD337505
4NS13K2DC	7.5	200	30.4	NSS33040	NSD33040
4NS13K3DC		230	26.4	NSS32432	NSD32432
4NS13K4DC		460	13.2	NSS31318	NSD31318
4NS13K5DC		575	10.6	NSS390145	NSD390145
4NS13L2AC	10	200	40	NSS3750	NSD33750
4NS13L3AC		230	34.8	NSS33040	NSD33040
4NS13L4AC		460	17.4	NSS31723	NSD31723
4NS13L5AC		575	13.9	NSS313185	NSD313185

