

REPAIR PARTS

RRJENDUR2 R2

 REDJACKET SERIES

4" Enduro REPAIR PARTS


50 AND 60 HZ - PUMPS WITH HEX SHAFTS BUILT AFTER Q1, 2008

ENDURO 60 HZ PUMPS WITH HEX SHAFTS BUILT AFTER Q1, 2008


Item No.	Description	Current Model					
	Number of Stages	HP	6S (4)	8S (5)	12S	20S	25S
		½R	-	-	8	-	-
		½	17	12	9	5	-
		¾	21 (1)	16	12	6	-
		1	25 (1)	21 (2)	14	8	7
		1½	32 (1)	25 (2)	18 (2)	11	10
		2	-	30 (2)	23 (2)	14	12
		3	-	43 (3)	32 (2)	19 (2)	17
	5	-	-	-	30 (2)	28 (2)	
1	Discharge head/CV assembly		7K2997				
2	Check valve assembly		7K2359				
3	Upper retaining ring		7K817	-	-	-	-
4	Shim - 0.020		7K155	-	-	-	-
5	Shim - 0.042		7K2365	-	-	-	-
6	Upper bearing housing		7K2361				
7	Upper bearing		7K3059				
8	0.300 Adapter ring (1)(2)		7K2360				
9	0.400 Adapter ring		7K2363	-	-	-	-
10	Machined stage assembly (4)(5)		7K3252	7K3254	-	-	-
11	Stage assembly		7K3251	7K3253	7K3255	7K3256	7K3257
12	Intermediate bearing hsg. (1)(2)(3)		7K2369				
13	Intermediate bearing (1)(2)(3)		7K3231				
14	Intermediate shaft sleeve (1)(2)(3)		7K209	7K3056			
15	Lower shaft sleeve		7K1320	7K1336			
16	Lower adapter ring		7K2372				
17	Motor adapter		7K2374				
18	Inlet strainer		7K2375				
19	Cable guard screw		13K91				
20	Casing	½R	-	-	7K2519	-	-
		½	7K2534	7K2325	7K2521	7K2316	-
		¾	7K2539	7K2532	7K2526	7K2517	-
		1	7K2544	7K2537	7K2528	7K2519	7K2520
		1½	7K2550	7K2542	7K2535	7K2524	7K2527
		2	-	7K2547	7K2541	7K2528	7K2529
		3	-	7K2552	7K2550	7K2536	7K2537
21	Shaft assembly	5	-	-	-	7K2548	7K2551
		½R	-	-	7K3263	-	-
		½	7K3243	7K3270	7K3267	7K3219	-
		¾	7K3241	7K3277	7K3271	7K3260	-
		1	7K3290	7K3234	7K3237	7K3263	7K3265
		1½	7K3298	7K3288	7K3279	7K3269	7K3271
		2	-	7K3293	7K3286	7K3237	7K3273
22	Cable Guard	3	-	7K3302	7K3300	7K3281	7K3234
		5	-	-	-	7K3294	7K3301
		½R	-	-	7K2481	-	-
		½	7K2496	7K2487	7K2483	7K2478	-
		¾	7K2501	7K2494	7K2488	7K2479	-
		1	7K2505	7K2499	7K2490	7K2481	7K2482
		1½	7K2512	7K2504	7K2497	7K2485	7K2488
		2	-	7K2508	7K2503	7K2490	7K2491
		3	-	7K2514	7K2512	7K2498	7K2499
		5	-	-	-	7K2510	7K2513

Residential Water Systems


- (1) Model requires one intermediate bearing housing, intermediate bearing, intermediate shaft sleeve, a 0.300 adapter ring and an intermediate retainer ring. Order parts separately.
- (2) Model requires one intermediate bearing housing, intermediate bearing and an intermediate shaft sleeve. Order parts separately.
- (3) Model requires two each of the following: Intermediate bearing housing, intermediate bearing and an intermediate shaft sleeve. Order parts separately.
- (4) Model requires at least one machined stage assembly at upper retaining ring. Models that have an intermediate bearing also require one machined stage assembly at each required intermediate bearing. Number of stages includes required machined stage assemblies.
- (5) Model requires one machined stage assembly. Number of stages includes required machined stage assembly.



6S - 5 GPM



8S - 7 GPM
12S - 10 GPM
20S - 18 GPM
25S - 22 GPM



TYP. ALL MODELS

ENDURO 50 HZ PUMPS WITH HEX SHAFTS BUILT AFTER Q1, 2008

Item No.	Description	Current Model					
	Number of Stages	HP	AE (4)	VB	BC	CC	GC
		½	15	-	9	5	-
		¾	22 (1)	-	12	8	6
		1	29 (1)	-	15	10	9
		1½	44 (1)	-	19 (2)	14	13
		2	-	-	25 (2)	19 (2)	17
		3	-	-	32 (2)	26 (2)	26 (2)
		5	-	-	-	-	-
1	Discharge head/CV assembly		7K2998				
2	Check valve assembly		7K2359				
3	Upper retaining ring		7K817	-	-	-	
4	Shim - 0.020		7K155	-	-	-	
5	Shim - 0.042		7K2365	-	-	-	
6	Upper bearing housing		7K2361				
7	Upper bearing		7K3059				
8	0.300 Adapter ring (1)(2)		7K2360				
9	0.400 Adapter ring		7K2363	-	-	-	
10	Machined stage assembly (4)(5)		7K3252	7K3254	-	-	
11	Stage assembly		7K3251	7K3253	7K3255	7K3256	7K3257
12	Intermediate bearing hsg. (1)(2)(3)		7K2369				
13	Intermediate bearing (1)(2)(3)		7K3231				
14	Intermediate shaft sleeve (1)(2)(3)		7K209	7K3056			
15	Lower shaft sleeve		7K1320	7K1336			
16	Lower adapter ring		7K2372				
17	Motor adapter		7K2374				
18	Inlet strainer		7K2375				
19	Cable guard screw		13K91				
20	Casing	½	7K2531	-	7K2521	7K2516	-
		¾	7K2540	-	7K2526	7K2519	7K2518
		1	7K2546	-	7K2530	7K2522	7K2523
		1½	7K2553	-	7K2536	7K2528	7K2533
		2	-	-	7K2543	7K2536	7K2537
		3	-	-	7K2550	7K2545	7K2549
		5	-	-	-	-	-
21	Shaft assembly	½	7K3275	-	7K3266	7K3219	-
		¾	7K3249	-	7K3270	7K3263	7K3245
		1	7K3238	-	7K3274	7K3268	7K3269
		1½	7K3303	-	7K3280	7K3237	7K3276
		2	-	-	7K3289	7K3281	7K3234
		3	-	-	7K3297	7K3291	7K3295
		5	-	-	-	-	-
22	Cable Guard	½	7K2492	-	7K2483	7K2478	-
		¾	7K2502	-	7K2488	7K2481	7K2480
		1	7K2453	-	7K2492	7K2484	7K2485
		1½	7K2515	-	7K2498	7K2490	7K2494
		2	-	-	7K2505	7K2498	7K2499
		3	-	-	7K2512	7K2507	7K2511
		5	-	-	-	-	-



Xylem Inc.
 2881 East Bayard Street Ext., Suite A
 Seneca Falls, NY 13148
 Phone: (866) 325-4210
 Fax: (888) 322-5877
goulds.com/brands/redjacket

Goulds is a registered trademark of Goulds Pumps, Inc. and is used under license. Red Jacket Water Products and Enduro are trademarks of Xylem Inc. or one of its subsidiaries.
 © 2021 Xylem Inc. RRJENDUR2 R2 August 2021