

3885

PUMP TO PANEL PART NUMBERS

Pump	HP	Phase	Voltage	Amps	Simplex Panel	Duplex Panel
WE0311L	0.33	1	115	10.7	C4S10020	C4D10020
WE0318L	0.33	1	208	6.8	C4S10020	C4D10020
WE0312L	0.33	1	230	4.9	C4S10020	C4D10020
WE0311M	0.33	1	115	10.7	C4S10020	C4D10020
WE0318M	0.33	1	208	6.8	C4S10020	C4D10020
WE0312M	0.33	1	230	4.9	C4S10020	C4D10020
WE0511H	0.5	1	115	14.5	C4S10020	C4D10020
WE0518H	0.5	1	208	8.1	C4S10020	C4D10020
WE0512H	0.5	1	230	7.3	C4S10020	C4D10020
WE0538H	0.5	3	200	4.9	C4S34063	C4D34063
WE0532H	0.5	3	230	3.3	C4S32540	C4D32540
WE0534H	0.5	3	460	1.7	C4S31625	C4D31625
WE0537H	0.5	3	575	1.4	C4S31625	C4D31625
WE0511HH	0.5	1	115	14.5	C4S10020	C4D10020
WE0518HH	0.5	1	208	8.1	C4S10020	C4D10020
WE0512HH	0.5	1	230	7.3	C4S10020	C4D10020
WE0538HH	0.5	3	200	4.9	C4S34063	C4D34063
WE0532HH	0.5	3	230	3.6	C4S32540	C4D32540
WE0534HH	0.5	3	460	1.8	C4S31625	C4D31625
WE0537HH	0.5	3	575	1.5	C4S31625	C4D31625
WE0718H	0.75	1	208	11	C4S10020	C4D10020
WE0712H	0.75	1	230	10	C4S10020	C4D10020
WE0738H	0.75	3	200	6.2	C4S36310	C4D36310
WE0732H	0.75	3	230	5.4	C4S34063	C4D34063
WE0734H	0.75	3	460	2.7	C4S32540	C4D32540
WE0737H	0.75	3	575	2.2	C4S31625	C4D31625
WE1018H	1	1	208	14	C4S10020	C4D10020
WE1012H	1	1	230	12.5	C4S10020	C4D10020
WE1038H	1	3	200	8.1	C4S36310	C4D36310
WE1032H	1	3	230	7	C4S36310	C4D36310
WE1034H	1	3	460	3.5	C4S32540	C4D32540
WE1037H	1	3	575	2.8	C4S32540	C4D32540
WE1518H	1.5	1	208	17.5	C4S10020	C4D10020

Pump	HP	Phase	Voltage	Amps	Simplex Panel	Duplex Panel
WE1512H	1.5	1	230	15.7	C4S10020	C4D10020
WE1538H	1.5	3	200	10.6	C4S31016	C4D31016
WE1532H	1.5	3	230	9.2	C4S36310	C4D36310
WE1534H	1.5	3	460	4.6	C4S34063	C4D34063
WE1537H	1.5	3	575	3.7	C4S32540	C4D32540
WE1518HH	1.5	1	208	17.5	C4S10020	C4D10020
WE1512HH	1.5	1	230	15.7	C4S10020	C4D10020
WE1538HH	1.5	3	200	10.6	C4S31016	C4D31016
WE1532HH	1.5	3	230	9.2	C4S36310	C4D36310
WE1534HH	1.5	3	460	4.6	C4S34063	C4D34063
WE1537HH	1.5	3	575	3.7	C4S32540	C4D32540
WE2012H	2	1	230	18	C4S10020	C4D10020
WE2038H	2	3	200	12	C4S31016	C4D31016
WE2032H	2	3	230	11.6	C4S31016	C4D31016
WE2034H	2	3	460	5.8	C4S34063	C4D34063
WE2037H	2	3	575	4.7	C4S34063	C4D34063



Xylem Inc.
 2881 East Bayard Street Ext., Suite A
 Seneca Falls, NY 13148
 Phone: (866) 325-4210 • Fax: (888) 322-5877
www.xylem.com/goulds

Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are property of their respective owners.
 © 2024 Xylem Inc. GWTC43885-PL129 R1 April 2024