



xylem

Fire pump systems

For the protection of life and property, A-C Fire Pump offers package systems that meet every fire protection need.



A-C Fire Pump Systems and Professional Fire Protection...



One of the first built fire trucks in the late 1800's was equipped with an A-C Fire pump.

A Shared Tradition of Excellence

One of the first fire trucks built in the late 1800's was equipped with an A-C Fire Pump. For over 100 years, A-C Fire Pump Systems has been on the forefront in developing, designing and custom-building a wide range of fire pump systems including prefabricated packages and house units that meet every fire protection need. A-C Fire Pump is not only rich in history, but on the cutting edge of new technology as demonstrated with our contribution to the fire protection systems for launch pads 39A and 39B for NASA at the Kennedy Space Center. A-C Fire Pump Systems furnished a package of four 12x8x22 9100 series horizontal splitcase pumps driven by huge 1065 horsepower diesel engines including state-of-the-art control systems. Each pump is rated at 3,500 gallons per minute at 250 psi pressure. We will continue to be the leader in the fire protection industry providing both excellent service and superior products for years to come. You can always count on A-C Fire Pump Systems to solve your pumping problems.

Versatility – a key word at A-C Fire Pump Systems.

We realize that each customer has different fire protection needs, specific to each fire hazard. We can design a system around your needs – special buildings, pump materials and custom floor arrangements. You need it – we'll provide it.



To protect the space shuttle launch facilities, NASA installed a fail-safe fire suppression system utilizing A-C Fire pumps.



In-Line Pumps

Capacity to 1500 GPM (5,678 L/min)

Pressures to 165 PSI (116 m) • Working Pressures to 150 PSI


- Space saving design
- No foundation or pads required.
- Suction and discharge flanges are on a common centerline, 180° apart for inline mounting in piping
- Top pullout design allows for fast and easy servicing. The rotating element is easily removed without disturbing suction and discharge piping.
- Self-venting design eliminates the need for an automatic air release valve.
- Bronze impeller is dynamically balanced and keyed direct to themotor shaft.

End Suction Pumps

Capacity to 500 GPM (1,892 L/min)

Pressures to 150 PSI (106 m) • Working Pressures to 250 PSI

- Top centerline discharge with foot supported casing.
 - Ease of installation
 - Simplifies piping layout
 - Reduces problems associated with piping strain
- Self-venting design eliminates the need for automatic air release valve.
- Rear pullout design supplied as standard with spacer coupling.
 - Ease of maintenance, eliminates disturbing driver or piping when removing rotating element.
- Hydraulically balanced impeller extends bearing life and assures smoother operation.
- Available in electric motor or diesel engine driven configuration.




Vertical Turbine Pumps

Capacity to 5000 GPM (18,925 L/min) • Pressures to 350 PSI (247 m)

Working Pressures

- up to 200 PSI with 125 lb. A.S.A. flanges
- up to 550 PSI with 250 lb. A.S.A. flanges
- Required by NFPA when operating under a static suction lift condition.
- Dynamically balanced impellers secured to the shaft with steel locking collets to assure proper problem free operation.
- Open lineshaft design provides for product lubrication of the bearings.
- Available in electric motor or diesel engine driven configuration.
- Provided with a bronze suction strainer as standard.
- Provided with an oversized air release valve as standard.
- Available in special materials of construction for salt water applications.





Split Case Pumps – Single Stage


8100 Series

Capacity to 3000 GPM (11,355 L/min) • Pressures to 255 PSI (179 m)

Working Pressures

- up to 250 PSI (176 m) with 125 lb. A.S.A. flanges
- up to 375 PSI (264 m) with 250 lb. A.S.A. flanges

- Space saving design
- Available in horizontal or vertical configuration
- Suction and discharge flanges are on a common centerline
- Bearing span is kept to a minimum
- Available in electric motor driven or engine driven configuration
- Available in clockwise or counter-clockwise rotation to simplify pump room layout




8150 Series

Capacity to 5000 GPM (18,925 L/min) • Pressures to 233 PSI (157 m)

Working Pressures

- up to 250 PSI (123 m) with 125 lb. A.S.A. flanges
- up to 325 PSI (180 m) with 250 lb. A.S.A. flanges

- Space saving design
- Suction and discharge flanges are on a common centerline
- Dual volute casing balances radial forces on the shaft and bearings
- Available in electric motor driven or engine driven configuration
- Available in clockwise or counter-clockwise rotation to simplify pump room layout



9100 Series

Capacity to 5000 GPM (18,925 L/min) • Pressures to 208 PSI (146 m)

Working Pressures

- up to 175 PSI (123 m) with 125 lb. A.S.A. flanges
- up to 255 PSI (180 m) with 250 lb. A.S.A. flanges

- Space saving design
- Suction and discharge flanges are on a common centerline
- Dual volute casing balances radial forces on the shaft and bearings
- Available in electric motor driven or engine driven configuration
- Available in clockwise or counter-clockwise rotation to simplify pump room layout



Split Case Pumps – Two Stage

8200 Series

Capacity to 1000 GPM (3,785 L/min) • Pressures to 640 PSI (450 m)

Working Pressures

- up to 500 PSI (352 m) with 250 lb. A.S.A. flanges
- up to 800 PSI (563 m) with 800 lb. A.S.A. flanges

- Space saving design
- Suction and discharge flanges are on a common centerline
- Bearing span is kept to a minimum
- Compact pump design
- Dual volute casing balances radial forces on the shaft and bearings
- Available in electric motor driven or engine driven configuration
- Two stage pump with two impellers threaded together
- Dynamic balanced impellers
- Available in clockwise or counter-clockwise rotation to simplify pump room layout

Xylem
8200 N. Austin Avenue
Morton Grove, Illinois 60053

Tel +1 847.966.3700
Fax +1 847.965.8379
www.xylem.com/acfirepump

All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products. Subject to change without notice.

© 2025 Xylem Inc. or its affiliates. All rights reserved. Xylem and A-C Fire Pump are trademarks or registered trademarks of Xylem Inc. or one of its subsidiaries. All other trademarks or registered trademarks are the property of their respective owners.

ACF VT BRO 5211829 R5 March 2025

xylem
Let's Solve Water