




MOTOR FRAMES	C	MO	HD	HA	HB	HE	HF 1	HF
215	19.00	6.00	14.29	20.00	48.00	9.00	18.00	36.00
254	21.37	7.12						
256	23.12	7.12						
284	24.62	7.75						
286	26.12	7.75						
324	27.75	8.62						

NOTES

1. All Dimensions are in inches with $\pm .125$ " tolerance unless otherwise specified.
2. Suction and discharge connections are 125# ANSI B16.1 standard flanges. Holes in flanges straddle $\varnothing$. (See Note 6)
3. Baseplate setting (before piping), grouting procedures and final alignment must in accordance with A-C Fire Pump Systems recommended procedures outlined in the Instruction Manual associated with this pump type.
4. Motor dimensions are approximate for a given NEMA frame. Consult factory if space is limited.
5. Both suction and discharge pipes must be supported independently near the pump to reduce strain on the pump casing.
Also expansion joints, if used, must not exert force on casting.
6. Coupling guard to meet ANSI/OSHA requirements.

NOT FOR CONSTRUCTION, INSTALLATION OR APPLICATION PURPOSES UNLESS CERTIFIED.								
CERTIFIED FOR:							UL FM ULC APPROVAL ☐ ☐ ☐	
CUSTOMER ORDER NO:			IDENTIFICATION NO:				FLANGES	
PUMP DATA	SIZE	MODEL	CURVE NO.	GPM	HEAD (FT)	ROTATION	SUCTION	FLANGES
MOTOR DATA	HP	RPM	VOLTS	PHASE	HERTZ	FRAME SIZE	ENCLOSURE	
SHOP ORDER:			CERTIFIED BY:			DATE		