


ALL DIMENSIONS IN INCHES

SUPERSEDES ALL PREVIOUS ISSUES



ALL DIMENSIONS IN INCHES

SUPERSEDES ALL PREVIOUS ISSUES

	PUMP	ENGINE	"A"	"B"	"B1"	"B2"	"C"	"D"	"F"	"H"	"J"	"L"	"M"	"R&U"	"BB"	"CC"	"W"
⑦	10x8x17F 8100	CFP11E-F10	118.48	10.19	75.43	56.03	17	22.56	29.88	16	38.45	18	16	10	120	54	14.25
⑦	10x8x20F 8100	CFP11E-F10	118.48	10.19	75.43	56.03	17	22.56	29.88	20	38.45	20	18	14	120	54	14.25
		CFP11E-F20															
⑦	12x10x18F 8100	CFP11E-F10	118.48	10.19	75.43	56.03	17	22.56	29.88	18	38.45	20	18	11	120	54	14.25
		CFP11E-F20															

	PUMP	ENGINE	"A"	"B"	"B1"	"B2"	"C"	"D"	"F"	"H"	"J"	"L"	"M"	"R&U"	"BB"	"CC"	"W"
⑦	12x8x21F 9100	CFP11E-F10	128.92	4.50	75.43	56.03	21.75	28.25	29.88	19	38.45	21	21	12	120	54	14.25
		CFP11E-F20															
	12x8x22F-M 9100	CFP11E-F10	128.92	4.50	75.43	56.03	21.75	28.25	29.88	19	38.45	21	21	12	120	54	14.25
		CFP11E-F20															
⑦	14x10x20F 9100	CFP11E-F10	133.17	14.25	75.43	56.03	23.75	30.50	32.88	21	38.45	21	19	13	132	60	14.25
		CFP11E-F20															
⑦	16x12x23F 9100	CFP11E-F10	133.17	14.25	75.43	56.03	23.75	30.50	32.88	23	38.45	25	25	14	132	60	14.25
		CFP11E-F20															

NOTES

- All dimensions are inches $\pm .125$ " tolerance unless otherwise specified.
Caution
The UL listed drive shaft is not designed to operate at 0° angle.
The UL listing covers 2° $\pm 1^\circ$.
Refer to the engine manual for alignment
- Suction and discharge connections per ANSI B16.1. Holes in flanges straddle center line .
- Base plate setting (before piping), grouting procedures, and final alignment must be in accordance with A-C Fire Pump Systems recommended procedures outlined in the Instruction Manual associated with this pump type.
- Both suction and discharge pipes must be supported independently near the pump to reduce strain on the pump casing. Also expansion joints, if used must not exert force on the casing.
- Coupling guard to meet ANSI/OSHA requirements.
- Heater voltage requirements: 120 VAC, 240 VAC optional.
Do not energize until engine coolant has been installed.
- These units are available in both standard and high working pressures. Unit is denoted with an "H" prefix when specifying high working pressures. Example H6x4x11F. Refer to engineering data for actual working pressure values. High pressure pumps have 250 F.F. flanges per B16.1 unless noted.

NOT FOR CONSTRUCTION, INSTALLATION OR APPLICATION PURPOSES UNLESS CERTIFIED.								
CERTIFIED FOR:							APPROVAL UL ☐ FM ☐ ULC ☐	
CUSTOMER ORDER NO:				IDENTIFICATION NO:			FLANGES	
PUMP DATA	SIZE	MODEL	CURVE NO.	GPM	HEAD (FT.)	ROTATION	SUCTION	DISCHARGE
						CW		
ENGINE DATA	MAKE	MODEL	HP	RPM	VOLTAGE	POLARITY	MAX ALTITUDE	
	CUMMINS					NEG.		
SHOP ORDER:			CERTIFIED BY:			TOTAL WEIGHT		DATE: