


A-C Fire Pump Systems Motor Driven - FP 2.4



X	125# Discharge flange					
	A	DA	DB	DG	DK	DD
☐	4	7.50	8	5/8-11	0.75	8.25
☐	6	9.50	8	3/4-10	1.00	10.00
☐	8	11.75	8	3/4-10	1.00	11.00
☐	10	14.25	12	7/8-9	1.00	12.50

X	250# Discharge flange					
	A	DA	DB	DG	DK	DD
☐	4	7.88	8	3/4-10	1.00	8.50
☐	6	10.63	12	3/4-10	1.38	10.38
☐	8	13.00	12	7/8-9	1.50	11.50
☐	10	15.25	16	1-8	1.50	13.00

X	Model	No. of stages	B – 1st stage	B – add'l stage	C	E	F	K
☐	FP10WALC		22.26	7.63	12.25	6.63	11.25	4
☐	FP11CLC		25.26	9.88	13.25	6.25	12.13	6
☐	FP11CHC		25.26	9.88	13.25	6.25	12.13	6
☐	FP12CHC		28.26	11.00	13.25	6.25	12.13	6
☐	FP14RJHC		30.51	11.50	15.00	9.63	14.00	8
☐	FP14RHHC		42.51	13.63	15.00	11.38	13.75	10
☐	FP16DMC		52.25	15.25	19.00	16.00	17.50	10

X	Model	A	DH	HH	AD	G	J	H	Min. subm.
☐	FP10WALC	4	9.00	17.00	0.61	16.00	.75	14.25	23.93
☐	FP11CLC	6	9.00	21.00	0.88	19.00	.75	17.00	29.25
☐	FP11CHC	6	9.00	21.00	0.88	19.00	.75	17.00	33.75
☐	FP12CHC	6	9.00	21.00	0.88	19.00	.75	17.00	40.25
☐	FP14RJHC	8	9.00	21.00	0.88	21.00	.75	18.75	51.63
☐	FP14RHHC	10	10.50	26.00	0.88	23.50	.75	21.25	61.38
☐	FP16DMC	10	10.50	26.00	0.88	25.00	.75	21.25	66.00


Notes:

1. Dimensions based on motor height of a standard WP-1 hollow shaft motor. Subject to change depending on motor mfg. and/or the use of a motor adapter.
2. Dimensions are in inches unless otherwise indicated.
3. When motor is oil lubricated. Oil is not furnished. See operation manual for manufacturer's recommendations.

NOT FOR CONSTRUCTION, INSTALLATION OR APPLICATION PURPOSES UNLESS CERTIFIED

Certified for:				Approval: UL ☐ FM ☐ ULC ☐			
Customer order no.:				Identification no.:			
Pump data	Size	No. of stages	Curve no.	GPM	Head (PSI)	Rotation	Flanges
Motor data	HP	RPM	Volts	Phase	Hertz	Frame size	Enclosure
Shop order:			Certified by:		Total weight:		Date:

A-C Fire Pump Systems Motor Driven - FP 2.4



X	125# Discharge flange					
	A	DA	DB	DG	DK	DD
☐	12	17.00	12	.88-9	1.00	14.50
☐	14	18.75	12	1.125-7	1.38	22.00

X	Model	No. of stages	B – 1st stage	B – add'l stage	C	E	F	K
☐	FP18DMC		51.00	16.75	21.00	16.75	19.50	12
☐	FP18DHC		51.00	16.75	21.00	16.75	19.50	12
☐	FP20EHC		51.25	18.00	26.00	20.75	24.13	14

X	Model	A	DH	HH	AD	G	J	H	Min. subm.
☐	FP18DMC	12	12.00	31.00	0.88	27.50	.75	25.00	139.75
☐	FP18DHC	12	12.00	31.00	0.88	27.50	.75	25.00	237.75
☐	FP20EHC	14	13.00	34.50	1.25	32.00	1.38	29.50	91.75

Notes:

1. Dimensions based on motor height of a standard WP-1 hollow shaft motor. Subject to change depending on motor mfg. and/or the use of a motor adapter.
2. Dimensions are in inches unless otherwise indicated.
3. When motor is oil lubricated. Oil is not furnished. See operation manual for manufacturer's recommendations.

Supersedes all previous issues

NOT FOR CONSTRUCTION, INSTALLATION OR APPLICATION PURPOSES UNLESS CERTIFIED

Certified for:				Approval: UL ☐ FM ☐ ULC ☐			
Customer order no.:				Identification no:			
Pump data	Size	No. of stages	Curve no.	GPM	Head (PSI)	Rotation	Flanges
Motor data	HP	RPM	Volts	Phase	Hertz	Frame size	Enclosure
Shop order:			Certified by:		Total weight:		Date:

Xylem
8200 N. Austin Avenue
Morton Grove, Illinois 60053

Tel +1 847.966.3700
Fax +1 847.965.8379
www.xylem.com/acfirepump

All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products. Subject to change without notice.

© 2025 Xylem Inc. or its affiliates. All rights reserved. Xylem and A-C Fire Pump are trademarks or registered trademarks of Xylem Inc. or one of its subsidiaries. All other trademarks or registered trademarks are the property of their respective owners.

ACF-FP2.4 P202 SUB 590 R2 March 2025

xylem
Let's Solve Water