



Control Panel Schematic and Layout

BGSDD11522 R1

CONTROL PANEL SCHEMATIC



REVDATE: 0523

----- DASHED LINE INDICATES
FIELD WIRING.

USE COPPER CONDUCTORS ONLY.

TEMPERATURE RATING OF CONDUCTORS IS TO BE:
60°C (140°F) FOR UNDER 100A.
75°C (167°F) FOR OVER 100A.

BRANCH CIRCUIT PROTECTION SHALL BE PROVIDED BY THE INSTALLER: MUST BE SIZED ACCORDING TO PUMP/MOTOR MANUFACTURING SPECIFICATIONS.

VERIFY CORRECT OPERATION OF CONTROL PANEL AFTER
INSTALLATION IS COMPLETE.

FIELD WIRING TORQUE SPECS.	
TERMINAL BLOCK UT 2.5	5 IN-LB
TERMINAL BLOCK UT 4	7 IN-LB
TERMINAL BLOCK UT 6	15 IN-LB
TERMINAL BLOCK UT 10	15 IN-LB
TERMINAL BLOCK UT 16	25 IN-LB
TERMINAL BLOCK UT 35	30 IN-LB
TS1, TS2, J2 & J3 PCB	5 IN-LB
TRANSFORMER H1F, H2F & H3F	15 IN-LB
TRANSFORMER H1, H2 & H3	10 IN-LB
DS1 VLS3P16-63 R1	16 IN-LB
DS1 VLS3P63-125 R2	45 IN-LB
DS1 LK4J3CN 100A	36 IN-LB
DS1 LK4MU3N 200A	200 IN-LB

DRAWN BY:	AL	DATE:	05/18/23
APPROVED BY:	DO	DATE:	05/18/23

THIS DRAWING CONTAINS
PROPRIETARY INFORMATION
AND SHALL NOT BE USED
OR DISCLOSED WITHOUT
PRIOR WRITTEN
AUTHORIZATION.

DRAWN BY:	AL	DATE:	05/18/23
APPROVED BY:	DO	DATE:	05/18/23

THIS DRAWING CONTAINS
PROPRIETARY INFORMATION
AND SHALL NOT BE USED
OR DISCLOSED WITHOUT
PRIOR WRITTEN
AUTHORIZATION.


xylem
Let's Solve Water

3	TITLE:	SDD11522
		CONTROL PANEL SCHEMATIC

SIZE B	DWG NO. 4407	PART NO. SDD11522	REV.
SCALE NONE		SHEET 1 OF 2	

FNAME: SDD11522

REVDATE: 0523





----- DASHED LINE INDICATES FIELD WIRING.

USE COPPER CONDUCTORS ONLY.

TEMPERATURE RATING OF CONDUCTORS IS TO BE:
60°C (140°F) FOR UNDER 100A.
75°C (167°F) FOR OVER 100A.

BRANCH CIRCUIT PROTECTION SHALL BE PROVIDED BY THE INSTALLER; MUST BE SIZED ACCORDING TO PUMP/MOTOR MANUFACTURING SPECIFICATIONS.

VERIFY CORRECT OPERATION OF CONTROL PANEL AFTER INSTALLATION IS COMPLETE.



NOTE: FOR 208/240VAC OPERATION REMOVE WHITE JUMPER NEUTRAL REQUIRED FOR 120VAC CONTROL CIRCUIT


FIELD WIRING TORQUE SPECS.		DRAWN BY:		DATE:		Let's Solve Water					
TERMINAL BLOCK UT 2.5	5 IN-LB	AL		05/18/23							
TERMINAL BLOCK UT 4	7 IN-LB	APPROVED BY:		DATE:		TITLE: SDD11522 CONTROL PANEL SCHEMATIC					
TERMINAL BLOCK UT 6	15 IN-LB	DO		05/18/23							
TERMINAL BLOCK UT 10	15 IN-LB	THIS DRAWING CONTAINS PROPRIETARY INFORMATION AND SHALL NOT BE USED OR DISCLOSED WITHOUT PRIOR WRITTEN AUTHORIZATION.				SIZE B DWG NO. 4407 PART NO. SDD11522 REV					
TERMINAL BLOCK UT 16	25 IN-LB										
TERMINAL BLOCK UT 35	30 IN-LB										
TS1, TS2, J2 & J3 PCB	5 IN-LB										
TRANSFORMER H1F, H2F & H3F	15 IN-LB										
TRANSFORMER H1, H2 & H3	10 IN-LB										
DS1 VLS3P16-63 R1	16 IN-LB										
DS1 VLS3P63-125 R2	45 IN-LB										
DS1 LK4JU3CN 100A	36 IN-LB										
DS1 LK4MU3N 200A	200 IN-LB										
						SCALE NONE		SHEET 2 OF 2			

CONTROL PANEL LAYOUT

BGSDD11522 R1

FNAME: SDD11522

REVDATE: 0523



DRAWN BY:	AL	DATE:	05/18/23		
APPROVED BY:	DO	DATE:	05/18/23		
THIS DRAWING CONTAINS PROPRIETARY INFORMATION AND SHALL NOT BE USED OR DISCLOSED WITHOUT PRIOR WRITTEN AUTHORIZATION.				TITLE:	
				SDD11522	
				CONTROL PANEL LAYOUT	
SIZE	DWG NO.	PART NO.	REV		
B	4408	SDD11522			
SCALE	NONE	SHEET	1	OF 2	

CONTROL PANEL LAYOUT



FRAME: SDD11522

REVDATE: 0523

QTY	MANUFACTURER	DESCRIPTION	PART NUMBER	REF.
1	Saginaw	P.C. Nema 4X Enclosure 18x16x10	H161407HCLL	E1
1	Integra	Hinge Kit	US0PK-P909	N/A
1	All-Spec	Dead Front	520P	DF1
1	All-Spec	Back Panel	525	BP1
1	Ingram	Beacon	R10-SM	BE1
1	Ingram	Buzzer	PB-024-AD	B1
2	VCC	Red Light 125V	1050QC1	LT1-2
1	See Water	Display Board	GBJ5	GBJ5
5	LEDTRONICS	White Lense	LENS-LCD780-CWF	N/A
2	See Water	Flat Cable Assembly	IDC-25MB	N/A
2	Molex	4 Pin Connector	09-50-3041	N/A
1	Molex	6 Pin Connector	09-50-3061	N/A
1	See Water	Power Circuit Board	WWD	PCB1
2	Carling	HOA Toggle Switch	6FC57-73	TG1,2
2	Schneider	Circuit Breaker	M9F42230	CB1-2
2	Schneider	Side Mount Auxiliary	M9A26924	OL1-2
2	Schneider	Contactor	LC1D25JL	M1-2

QTY	MANUFACTURER	DESCRIPTION	PART NUMBER	REF.
1	Schneider	Circuit Breaker 3A 1 Pole	B1E1C6	CB3
1	Macromatics	Seal Fail Dual Channel Relay	SFP120C100	SFR1
1	Macromatics	8 Pin Socket	70169-D	SFR1
2	Trumeter	Elapsed Time Meter	6320-2500-0000	ETM1-2
2	Trumeter	Cycle Counter	6300-2500-0000	CC1-2
2	Phoenix Contact	Terminal Block UT-4	3044102	TB4
2	Phoenix Contact	Terminal Block UT-4-PE	3044128	G4-5
3	Phoenix Contact	Terminal Block UT-16	3044199	TB1
1	Phoenix Contact	Terminal Block UT-16-PE	3044212	G1
4	Phoenix Contact	Terminal Block UT-10	3044160	TB2-3
2	Phoenix Contact	Terminal Block UT-10-PE	3044173	G2-3
8	Phoenix Contact	End Stop	3022218	N/A
8	Phoenix Contact	End Cover UT-2.5-10	3047028	N/A
2	Phoenix Contact	End Cover UT-16	3047206	N/A
2	Altech	Angled Mounting Bracket	CA603	N/A
4	See Water	N.O. Narrow Angle Floats 50'	FPC0N50	N/A
1	UL	508A UL Label	N/A	N/A



DRAWN BY:	AL	DATE:	05/18/23		
APPROVED BY:	DO	DATE:	05/18/23		
THIS DRAWING CONTAINS PROPRIETARY INFORMATION AND SHALL NOT BE USED OR DISCLOSED WITHOUT PRIOR WRITTEN AUTHORIZATION.				TITLE:	
				SDD11522	
				CONTROL PANEL LAYOUT	
				SIZE	DWG. NO.
B	4408	SDD11522			
SCALE		NONE	SHEET		2 OF 2



Xylem Inc.
2881 East Bayard Street Ext.
Seneca Falls, NY 13148
Phone: (800) 453-6777
Fax: (888) 322-5877
www.xylem.com/bellgossett