





STAGE	FRAME (3-PHASE) TEFC			L2					DI (max.)	WEIGHTS (lb)				
		HP	L1	TEFC	L6	L7	L8	MI (ref.)	TEFC	LIQUID END	TEFC	HYDROVAR	DISCONNECT BOX	TOTAL WEIGHT
2	182-4TC	5	15.75	15.44	6.70	20.02	11.15	6.88	8.50	33	85	10	5	133
4		7-1/2	18.75			23.02				39	124			178
7	254TC	15	24.44	16.56		28.71		9.25	10.31	52	250			325

REV	ZONE	ID	DESCRIPTION	REV	ZONE	ID	DESCRIPTION	REV	ZONE	ID	DESCRIPTION

UNITS: INCHES

GENERAL TOLERANCES UNLESS NOTED OTHERWISE:

INCHES:	MILLIMETERS:
X.XX ± .020	X.X ± .50
X.XXX ± .005	X.XX ± .125

ANGLES: ALL ± .5°

GEOMETRIC TOLERANCES IN ACCORDANCE WITH ASME Y14.5M-1994 AND APPLICABLE GOULDS WATER TECHNOLOGY STANDARDS

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

// PARALLELISM
⊥ PERPENDICULARITY
∠ ANGULARITY
⌖ TRUE POSITION
↗ RUN OUT
↗↗ TOTAL RUN OUT (TIR)
◎ CONCENTRICITY
▱ FLATNESS
⌓ PROFILE

xylem
Let's Solve Water

PART: **ELEVATION DRAWING**

MODEL(S)	SIZE(S)				
HYDROVAR PKG SYS	4SV				
DRAWN: DP	DATE: 5/26	APPROVED: ES	DATE: TBD	GROUP:	
CAD: PRO/E	DRAWING: B00138C			REV:	
PATTERN:	MATERIAL: N/A	VOLUME: 1796.252	SCALE: 0.150	SHEET: 1 of 1	

Model: B00138C | Model Rev: 3 | Release Level: Released | DV: MV: | Date: 26-May-09 | DV: MV: 2