


JOB:	REPRESENTATIVE:
UNIT TAG:	ORDER NO.
ENGINEER:	SUBMITTED BY:
CONTRACTOR:	APPROVED BY:
	DATE:
	DATE:
	DATE:



# 6x8x17L

## Series HSC<sup>3</sup>

### Base Mounted - Double Suction Centrifugal Pumps

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_

HP \_\_\_\_\_ RPM \_\_\_\_\_

VOLTS \_\_\_\_\_

CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_

ENCLOSURE \_\_\_\_\_

APPROX. WEIGHT \_\_\_\_\_

SPECIALS \_\_\_\_\_

\_\_\_\_\_


\_\_\_\_\_

**MATERIALS OF CONSTRUCTION**

- Cast Iron Bronze Fitted
- Internally Self Flushing Mech. Seals
- Fabricated Heavy Duty Baseplate
- ANSI/OSHA Coupling Guard
- Flexible Coupling
- Spacer Coupling (Optional)
- Galvanized Drip Pan (Optional)

**TYPE OF SEAL**

- STANDARD SEAL CONSTRUCTION, 175 PSIG (12 BAR) WORKING PRESSURE, 125# ANSI FLANGE CONFIGURATION
- STANDARD:** Crane Type 21, BUNA/Carbon Ceramic, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
  - OPTIONAL:** Crane Type 21, EPR/Carbon Ceramic, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).
  - OPTIONAL:** Crane Type 21, EPR/Carbon Tungsten Carbide, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).



FLANGE DIMENSIONS IN INCHES	
Discharge	Suction
6	8

**DIMENSIONS - Inches (mm)**

MOTOR FRAME	HA	HB	2HE	HF <sub>1</sub>	HF <sub>2</sub>	HG	HH	HP	HR	CP	HC*	HD	HM*	HO	S & Z	VH	W	X	YY
284	24 (610)	62 (1575)	22 (559)	50 (1270)	25 (635)	4 (102)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	52 (1321)	21.25 (540)	29 (737)	32.8 (833)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
286	24 (610)	62 (1575)	22 (559)	50 (1270)	25 (635)	4 (102)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	53 (1346)	21.25 (540)	29 (737)	32.8 (833)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
324	24 (610)	62 (1575)	22 (559)	50 (1270)	25 (635)	4 (102)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	55 (1397)	21.25 (540)	30 (762)	32.8 (833)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
326	24 (610)	62 (1575)	22 (559)	50 (1270)	25 (635)	4 (102)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	56 (1422)	21.25 (540)	30 (762)	32.8 (833)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
364	24 (610)	68 (1727)	22 (559)	56 (1422)	28 (711)	4 (102)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	57 (1448)	21.25 (540)	31 (787)	32.8 (833)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
365	24 (610)	68 (1727)	22 (559)	56 (1422)	28 (711)	4 (102)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	58 (1473)	21.25 (540)	31 (787)	32.8 (833)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
404	24 (610)	68 (1727)	22 (559)	56 (1422)	28 (711)	4 (102)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	63 (1600)	21.25 (540)	32 (813)	32.8 (833)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
405	24 (610)	68 (1727)	22 (559)	68 (1422)	28 (711)	4 (102)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	65 (1651)	21.25 (540)	32 (813)	32.8 (833)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
444	24 (610)	76 (1930)	22 (559)	64 (1626)	32 (813)	6 (152)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	69 (1753)	23.25 (591)	35 (889)	34.8 (884)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)
445	24 (610)	76 (1930)	22 (559)	64 (1626)	32 (813)	6 (152)	1 (25)	6 (152)	5.62 (143)	26.19 (665)	71 (1803)	23.25 (591)	35 (889)	34.8 (884)	9 (229)	11.5 (292)	16.06 (408)	14 (356)	16 (406)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.  
 8200 N. Austin Avenue  
 Morton Grove, IL 60053  
 Phone: (847)966-3700 Fax: (847)965-8379  
 www.bellgossett.com

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.  
 © 2016 Xylem Inc.

