


JOB:	REPRESENTATIVE:	
UNIT TAG:	SUBMITTED BY:	DATE:
ENGINEER:	APPROVED BY:	DATE:
CONTRACTOR:		

VARIABLE SPEED PUMPING SYSTEMS
PRODUCT DATA BULLETIN
CABINET MOUNTED PUMP CONTROL SYSTEM



SPECIFICATIONS

The Technologic Pump Logic Controller, Adjustable Frequency Drive(s) and Bypass circuitry (optional) shall be mounted on a single door, NEMA-1 enclosure and be prewired at the factory to permit a single electrical power connection. A disconnect switch shall be provided for each AFD. The entire assembly shall be ETL listed. The enclosure shall be designed to be wall mounted. All functions of the components shall be tested and approved at the factory prior to shipment. Input power wiring and wiring from the cabinet to the motors shall be provided by the electrical contractor. Wiring from sensors to the cabinet shall be provided by the controls contractor.

SYSTEM SUMMARY

Total Capacity	Open System	_____	Discharge Pressure
_____ GPM		_____	Suction Pressure
	Closed System	_____	FT TDH
Power Supply	V/	PH/	HZ
Input Power	_____	_____	_____

TECHNOLOGIC 5500 PUMP LOGIC CONTROLLER

Number of zones _____

Flow sensor included?

☐ Yes ☐ No

Pump Staging (Valid on multiple pump, multiple AFD systems only)

☐ Yes ☐ No

ADJUSTABLE FREQUENCY DRIVE(S)

Quantity	Output
☐ One	☐ PWM (Graham VLT 600 - 52 amps max.)
☐ Two	☐ PWM (AAB - 96 amps max.)
☐ Three (No Bypass Allowed)	☐ PWM (AC Technologies - 124 amps max.)
Horsepower: _____ Voltage: _____ Amps: _____	☐ PWM (Square D - 124 amps max.)

AFD BYPASS/TRANSFER OPTION

☐ Automatic Type I ☐ Automatic Type III ☐ No Bypass
☐ Automatic Type II ☐ Automatic Type IV

SENSOR/TRANSMITTER

Qty. _____ TYPE _____
 Qty. _____ TYPE _____

PUMP/MOTOR

Qty.	GPM	TDH	HP	RPM	MODEL
_____	_____	_____	_____	_____	_____
_____	_____	_____	_____	_____	_____
Specials:	_____				