


JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



6x8x10A

Series HSC³

Base Mounted - Double Suction Centrifugal Pumps

SPECIFICATIONS


FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____



MATERIALS OF CONSTRUCTION

- ☒ Cast Iron Bronze Fitted
- ☒ Internally Self Flushing Mech. Seals
- ☒ Fabricated Heavy Duty Baseplate
- ☒ ANSI/OSHA Coupling Guard
- ☒ Flexible Coupling
- ☐ Spacer Coupling (Optional)
- ☐ Galvanized Drip Pan (Optional)

TYPE OF SEAL

- STANDARD SEAL CONSTRUCTION, 175 PSIG (12 BAR) WORKING PRESSURE, 125# ANSI FLANGE CONFIGURATION
- ☐ **STANDARD:** Crane Type 21, BUNA/Carbon Ceramic, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
 - ☐ **OPTIONAL:** Crane Type 21, EPR/Carbon Ceramic, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).
 - ☐ **OPTIONAL:** Crane Type 21, EPR/Carbon Tungsten Carbide, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).





FLANGE DIMENSIONS
IN INCHES

Discharge	Suction
6	8

DIMENSIONS - Inches (mm)

MOTOR FRAME	HA	HB	2HE	HF ₁	HF ₂	HG	HH	HP	HR	CP	HC*	HD	HM*	HO	S & Z	VH	W	X	YY
215	24.00 (610)	58.00 (1473)	22.00 (559)	46.00 (1168)	23.00 (584)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	60.25 (1530)	21.25 (540)	43.00 (1092)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)
254	24.00 (610)	64.00 (1626)	22.00 (559)	52.00 (1321)	26.00 (660)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	62.25 (1581)	21.25 (540)	45.00 (1143)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)
256	24.00 (610)	64.00 (1626)	22.00 (559)	52.00 (1321)	26.00 (660)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	64.25 (1632)	21.25 (540)	47.00 (1194)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)
284	24.00 (610)	64.00 (1626)	22.00 (559)	52.00 (1321)	26.00 (660)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	65.25 (1657)	21.25 (540)	48.00 (1219)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)
286	24.00 (610)	64.00 (1626)	22.00 (559)	52.00 (1321)	26.00 (660)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	67.25 (1708)	21.25 (540)	50.00 (1270)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)
324	24.00 (610)	64.00 (1626)	22.00 (559)	52.00 (1321)	26.00 (660)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	68.25 (1734)	21.25 (540)	51.00 (1295)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)
326	24.00 (610)	64.00 (1626)	22.00 (559)	52.00 (1321)	26.00 (660)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	69.25 (1759)	21.25 (540)	53.00 (1346)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)
364	24.00 (610)	68.00 (1727)	22.00 (559)	56.00 (1422)	28.00 (711)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	70.25 (1784)	21.25 (540)	55.00 (1397)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)
365	24.00 (610)	68.00 (1727)	22.00 (559)	56.00 (1422)	28.00 (711)	4.00 (102)	1.00 (25)	6.00 (152)	4.63 (118)	29.19 (741)	71.25 (1810)	21.25 (540)	56.00 (1422)	30.50 (775)	8.25 (210)	9.25 (235)	17.58 (447)	12.50 (318)	12.50 (318)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

*Motor dimensions are approximate for "T" frames, vary by manufacturer and motor type.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.xyleminc.com/brands/bellgossett

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2012 Xylem Inc.

xylem
Let's Solve Water