

JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:


SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



12x14x17-1/2L

VSCS Centrifugal Pumps

Base Mounted - Double suction

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

TYPE OF SEAL

Standard Seal Construction, 175 PSIG (12 Bar) working pressure, 125# ANSI flanges. External flush line to seal.

☐ Standard: Crane Type 2, Buna/Carbon-Ceramic, 120 psig (6 bar) max. suction pressure Temp. range: -20 to 225°F (-29 to 107 °C).

☐ Optional: Crane Type 2, EPR/Carbon-Tungsten 170 psig (12 bar) max. suction pressure, Temp. range: -20 to 250°F (-29 to 121 °C).

Standard Seal Construction, 300 PSIG (20 Bar) working pressure, 250# ANSI flanges.

☐ Optional: Crane Type 2, EPR/Carbon-Tungsten, 170 psig (12 bar) max. suction pressure Temp. range: -20 to 250°F (-29 to 121 °C).

-S Construction, 300 PSIG (20 Bar) working pressure, 250# ANSI flanges. External flush line to seal.

☐ Standard: -S Configuration, Durametallic RO, EPR/Carbon-Tungsten, 240 psig (16 bar) max. suction pressure, Temp. range: -20 to 300 °F* (-29 to 149 °C).

*For operating temperatures above 250°F, a cooled flush is required. On systems, cooling is accomplished by inserting the brazed plate heat exchanger kit in the flush line to cool the fluid.

MATERIALS OF CONSTRUCTION


☒ BRONZE FITTED

FEATURES

☒ ANSI/OSHA Coupling Guard

☒ Center Drop Out Spacer Coupling

☒ Fabricated Heavy Duty Baseplate



JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:


SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



12x14x17-1/2L

VSCS Centrifugal Pumps

Base Mounted - Double suction

SPECIFICATIONS

FLOW _____ HEAD _____
HP _____ RPM _____
VOLTS _____
CYCLE _____ PHASE _____
ENCLOSURE _____
APPROX. WEIGHT _____
SPECIALS _____

TYPE OF SEAL

Standard Seal Construction, 175 PSIG (12 Bar) working pressure, 125# ANSI flanges. External flush line to seal.

☐ Standard: Crane Type 2, Buna/Carbon-Ceramic, 120 psig (6 bar) max. suction pressure Temp. range: -20 to 225°F (-29 to 107 °C).

☐ Optional: Crane Type 2, EPR/Carbon-Tungsten 170 psig (12 bar) max. suction pressure, Temp. range: -20 to 250°F (-29 to 121 °C).

Standard Seal Construction, 300 PSIG (20 Bar) working pressure, 250# ANSI flanges.

☐ Optional: Crane Type 2, EPR/Carbon-Tungsten, 170 psig (12 bar) max. suction pressure Temp. range: -20 to 250°F (-29 to 121 °C).

-S Construction, 300 PSIG (20 Bar) working pressure, 250# ANSI flanges. External flush line to seal.

☐ Standard: -S Configuration, Durametallic RO, EPR/Carbon-Tungsten, 240 psig (16 bar) max. suction pressure, Temp. range: -20 to 300 °F* (-29 to 149 °C).


*For operating temperatures above 250°F, a cooled flush is required. On systems, cooling is accomplished by inserting the brazed place heat exchanger kit in the flush line to cool the fluid.


MATERIALS OF CONSTRUCTION

☒ BRONZE FITTED

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate





RIGHT HAND ROTATION IS FURNISHED UNLESS OTHERWISE SPECIFIED.

NOTE: EPDM COUPLINGS ARE STANDARD ON PUMPS WITH MOTOR FRAME SIZES THRU 324T.

FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	12" (305)	2" (51)	20" (508)
Suction	14" (356)	2-1/8" (54)	22-3/8" (568)

DIMENSIONS - Inches (mm)

MOTOR FRAME	DIMENSIONS - INCHES (MM)																	
	CP	HA	HB	HC MAX.	HD	2 HE	HF ₁	HF ₂	HH	HM MAX.	HO	HP	HR	S	W	X	YY	Z
404T	34 (864)	32 (813)	71 (1803)	76-5/8 (1946)	23-1/2 (597)	33 (838)	59 (1499)	29-1/2 (749)	1-1/8 (29)	35-3/8 (899)	45-1/4 (1149)	6 (152)	3-3/4 (95)	7-3/4 (197)	19-1/2 (495)	21-3/4 (552)	25 (635)	13-1/2 (343)
405T	34 (864)	32 (813)	71 (1803)	78-1/8 (1984)	23-1/2 (597)	33 (838)	59 (1499)	29-1/2 (749)	1-1/8 (29)	35-3/8 (899)	45-1/4 (1149)	6 (152)	3-3/4 (95)	7-3/4 (197)	19-1/2 (495)	21-3/4 (552)	25 (635)	13-1/2 (343)
444T	34 (864)	36 (914)	81 (2057)	83-1/4 (2115)	23-1/2 (597)	33 (838)	69 (1753)	34-1/2 (876)	1-1/8 (29)	36 (914)	45-1/4 (1149)	6 (152)	4-1/2 (114)	7-3/4 (197)	19-1/2 (495)	21-3/4 (552)	25 (635)	13-1/2 (343)
445T	34 (864)	36 (914)	81 (2057)	85-1/4 (2165)	23-1/2 (597)	33 (838)	69 (1753)	34-1/2 (876)	1-1/8 (29)	36 (914)	45-1/4 (1149)	6 (152)	4-1/2 (114)	7-3/4 (197)	19-1/2 (495)	21-3/4 (552)	25 (635)	13-1/2 (343)
444TS	34 (864)	36 (914)	81 (2057)	79-1/2 (2019)	23-1/2 (597)	33 (838)	69 (1753)	34-1/2 (876)	1-1/8 (29)	36 (914)	45-1/4 (1149)	6 (152)	4-1/2 (114)	7-3/4 (197)	19-1/2 (495)	21-3/4 (552)	25 (635)	13-1/2 (343)
445TS	34 (864)	36 (914)	81 (2057)	81-1/2 (2070)	23-1/2 (597)	33 (838)	69 (1753)	34-1/2 (876)	1-1/8 (29)	36 (914)	45-1/4 (1149)	6 (152)	4-1/2 (114)	7-3/4 (197)	19-1/2 (495)	21-3/4 (552)	25 (635)	13-1/2 (343)
250 HP & larger Consult Factory	34 (864)	36 (914)	*	*	23-1/2 (597)	33 (838)	*	*	1-1/8 (29)	*	45-1/4 (1149)	6 (152)	4-1/2 (114)	7-3/4 (197)	19-1/2 (495)	21-3/4 (552)	25 (635)	13-1/2 (343)

*Varies with Motor Manufacturer. 250HP and over consult factory.

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.bellgossett.com

xylem
Let's Solve Water

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2013 Xylem Inc.