


JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



4x6x10M

Series HSC³

Base Mounted - Double Suction Centrifugal Pumps

SPECIFICATIONS


FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

- ☒ Cast Iron Bronze Fitted
- ☒ Internally Self Flushing Mech. Seals
- ☒ Fabricated Heavy Duty Baseplate
- ☒ ANSI/OSHA Coupling Guard
- ☒ Flexible Coupling
- ☐ Spacer Coupling (Optional)
- ☐ Galvanized Drip Pan (Optional)

TYPE OF SEAL

- STANDARD SEAL CONSTRUCTION, 175 PSIG (12 BAR)
WORKING PRESSURE, 125# ANSI FLANGE CONFIGURATION
- ☐ **STANDARD:** Crane Type 21, BUNA/Carbon Ceramic, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
 - ☐ **OPTIONAL:** Crane Type 21, EPR/Carbon Ceramic, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).
 - ☐ **OPTIONAL:** Crane Type 21, EPR/Carbon Tungsten Carbide, 100 psig (6.8 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).

FLANGE DIMENSIONS
IN INCHES

Discharge	Suction
4	6

DIMENSIONS - Inches (mm)

MOTOR FRAME	HA	HB	2HE	HF ₁	HF ₂	HG	HH	HP	HR	CP	HC*	HD	HM*	HO	S & Z	VH	W	X	YY
182	24 (610)	48 (1219)	22 (559)	36 (914)	18 (457)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	37 (940)	18.25 (464)	24 (610)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
184	24 (610)	48 (1219)	22 (559)	36 (914)	18 (457)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	38 (965)	18.25 (464)	24 (610)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
213	24 (610)	48 (1219)	22 (559)	36 (914)	18 (457)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	41 (1041)	18.25 (464)	25 (635)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
215	24 (610)	48 (1219)	22 (559)	36 (914)	18 (457)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	43 (1092)	18.25 (464)	25 (635)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
254	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	45 (1143)	18.25 (464)	26 (660)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
256	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	47 (1194)	18.25 (464)	26 (660)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
284	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	48 (1219)	18.25 (464)	27 (686)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
286	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	50 (1270)	18.25 (464)	27 (686)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
324	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	51 (1295)	18.25 (464)	28 (711)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
326	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	52 (1321)	18.25 (464)	28 (711)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
364	24 (610)	64 (1626)	22 (559)	52 (1321)	26 (660)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	53 (1346)	18.25 (464)	29 (737)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
365	24 (610)	64 (1626)	22 (559)	52 (1321)	26 (660)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	54 (1372)	18.25 (464)	29 (737)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
404	24 (610)	64 (1626)	22 (559)	52 (1321)	26 (660)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	60 (1524)	18.25 (464)	30 (762)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
405	24 (610)	64 (1626)	22 (559)	52 (1321)	26 (660)	4 (102)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	61 (1549)	18.25 (464)	30 (762)	26.12 (663)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
444	24 (610)	76 (1930)	22 (559)	64 (1626)	32 (813)	6 (152)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	66 (1676)	20.25 (514)	32 (813)	28.12 (714)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)
445	24 (610)	76 (1930)	22 (559)	64 (1626)	32 (813)	6 (152)	1 (25)	6 (152)	4.62 (117)	22.81 (579)	68 (1727)	20.25 (514)	32 (813)	28.12 (714)	6.5 (165)	7.88 (200)	13.5 (343)	11.5 (292)	13 (330)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

*Motor dimensions are approximate for "T" frames, vary by manufacturer and type.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.xyleminc.com/brands/bellgossett

xylem
Let's Solve Water