


JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



6X8X12M

Series HSC-S

Base Mounted - Double Suction Centrifugal Pumps

SPECIFICATIONS


FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

- ☒ Cast Iron Bronze Fitted
- ☒ Fabricated Heavy Duty Baseplate
- ☒ ANSI/OSHA Coupling Guard
- ☒ Flexible Coupling
- ☐ Spacer Coupling (Optional)
- ☐ Galvanized Drip Pan (Optional)

TYPE OF SEAL

- ☐ **STANDARD:** 175 PSIG (12 Bar) working pressure, 125# ANSI Flange Configuration
- ☐ **STANDARD:** Crane Type 21, BUNA/Carbon Ceramic, 75 psig (5 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
- ☐ **OPTIONAL:** Crane Type 21, EPR/Carbon Ceramic, 75 psig (5 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).
- ☐ **OPTIONAL:** Crane Type 21, EPR/Carbon Tungsten Carbide, 75 psig (5 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).
- ☐ **OPTIONAL:** 280 PSIG (19 Bar) working pressure, 250# ANSI Flange Configuration
- ☐ **STANDARD:** Crane Type 1, BUNA/Carbon-Ceramic, 150 psig (10 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
- ☐ **OPTIONAL:** 400 PSIG (27 Bar) working pressure, 250# ANSI Flange Configuration
- ☐ **STANDARD:** Crane Type 1B, BUNA/Carbon-Ceramic, 300 psig (20 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
- ☐ **OTHER:**

**DIMENSIONS - Inches (mm)**

MOTOR FRAME	HA	HB	2HE	HF ₁	HF ₂	HG	HH	HP	HR	CP	HC*	HD	HM*	HO	S & Z	VH	W	X	YY
254	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	55 (1397)	21.25 (540)	28 (711)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
256	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	57 (1448)	21.25 (540)	28 (711)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
284	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	59 (1499)	21.25 (540)	29 (737)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
286	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	60 (1524)	21.25 (540)	29 (737)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
324	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	62 (1575)	21.25 (540)	30 (762)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
326	24 (610)	58 (1473)	22 (559)	46 (1168)	23 (584)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	63 (1600)	21.25 (540)	30 (762)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
364	24 (610)	64 (1626)	22 (559)	52 (1321)	26 (660)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	65 (1651)	21.25 (540)	31 (787)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
365	24 (610)	64 (1626)	22 (559)	52 (1321)	26 (660)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	66 (1676)	21.25 (540)	31 (787)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
404	24 (610)	64 (1626)	22 (559)	52 (1321)	26 (660)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	70 (1778)	21.25 (540)	32 (813)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
405	24 (610)	64 (1626)	22 (559)	52 (1321)	26 (660)	4 (102)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	72 (1829)	21.25 (540)	32 (813)	31 (787)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
444	24 (610)	76 (1930)	22 (559)	64 (1626)	32 (813)	6 (152)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	76 (1930)	23.25 (591)	35 (889)	33 (838)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
445	24 (610)	76 (1930)	22 (559)	64 (1626)	32 (813)	6 (152)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	78 (1981)	23.25 (591)	35 (889)	33 (838)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)
447	24 (610)	76 (1930)	22 (559)	64 (1626)	32 (813)	6 (152)	1 (25)	6 (152)	4.63 (118)	33.12 (841)	81 (2057)	23.25 (591)	35 (889)	33 (838)	9 (229)	9.6 (244)	18.5 (470)	14 (356)	14 (356)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.xyleminc.com/brands/bellgossett

xylem
Let's Solve Water

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2012 Xylem Inc.