


JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



4x6x10A

Series HSC-S

Base Mounted - Double Suction Centrifugal Pumps

SPECIFICATIONS


FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____



MATERIALS OF CONSTRUCTION

- ☒ Cast Iron Bronze Fitted
- ☒ Fabricated Heavy Duty Baseplate
- ☒ ANSI/OSHA Coupling Guard
- ☒ Flexible Coupling
- ☐ Spacer Coupling (Optional)
- ☐ Galvanized Drip Pan (Optional)

TYPE OF SEAL

- ☐ **STANDARD:** 175 PSIG (12 Bar) working pressure, 125# ANSI Flange Configuration
- ☐ **STANDARD:** Crane Type 21, BUNA/Carbon Ceramic, 75 psig (5 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
- ☐ **OPTIONAL:** Crane Type 21, EPR/Carbon Ceramic, 75 psig (5 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).
- ☐ **OPTIONAL:** Crane Type 21, EPR/Carbon Tungsten Carbide, 75 psig (5 Bar) maximum suction pressure, from -20° to 250°F (-29 °C to 121 °C).
- ☐ **OPTIONAL:** 280 PSIG (19 Bar) working pressure, 250# ANSI Flange Configuration
- ☐ **STANDARD:** Crane Type 1, BUNA/Carbon-Ceramic, 150 psig (10 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
- ☐ **OPTIONAL:** 400 PSIG (27 Bar) working pressure, 250# ANSI Flange Configuration
- ☐ **STANDARD:** Crane Type 1B, BUNA/Carbon-Ceramic, 300 psig (20 Bar) maximum suction pressure, from -20° to 225°F (-29 °C to 107 °C).
- ☐ **OTHER:**





FLANGE DIMENSIONS IN INCHES

Discharge	Suction
4	6

DIMENSIONS - Inches (mm)

MOTOR FRAME	HA	HB	2HE	HF ₁	HF ₂	HG	HH	HP	HR	CP	HC*	HD	HM*	HO	S & Z	VH	W	X	YY
182	21.50 (546)	48.00 (1219)	19.50 (495)	36.00 (914)	18.00 (457)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	55 (1397)	18.25 (464)	23.55 (598)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)
184	21.50 (546)	48.00 (1219)	19.50 (495)	36.00 (914)	18.00 (457)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	56 (1422)	18.25 (464)	23.55 (598)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)
213	21.50 (546)	48.00 (1219)	19.50 (495)	36.00 (914)	18.00 (457)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	59 (1499)	18.25 (464)	24.25 (616)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)
215	21.50 (546)	48.00 (1219)	19.50 (495)	36.00 (914)	18.00 (457)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	60 (1524)	18.25 (464)	24.25 (616)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)
254	21.50 (546)	60.00 (1524)	19.50 (495)	48.00 (1219)	24.00 (610)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	64 (1626)	18.25 (464)	25.35 (644)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)
256	21.50 (546)	60.00 (1524)	19.50 (495)	48.00 (1219)	24.00 (610)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	66 (1676)	18.25 (464)	25.35 (644)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)
284	21.50 (546)	60.00 (1524)	19.50 (495)	48.00 (1219)	24.00 (610)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	66 (1676)	18.25 (464)	26.05 (662)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)
286	21.50 (546)	60.00 (1524)	19.50 (495)	48.00 (1219)	24.00 (610)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	67 (1702)	18.25 (464)	26.05 (662)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)
324	21.50 (546)	60.00 (1524)	19.50 (495)	48.00 (1219)	24.00 (610)	4.00 (102)	1.00 (25)	6.00 (152)	2.88 (73)	30.06 (764)	69 (1753)	18.25 (464)	26.85 (682)	25.94 (659)	7.00 (178)	7.69 (195)	17.25 (438)	11.50 (292)	12.00 (305)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

*Motor dimensions are approximate for "T" frames, vary by manufacturer and motor type.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.xyleminc.com/brands/bellgossett

xylem
Let's Solve Water

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2012 Xylem Inc.