

JOB:
REPRESENTATIVE:

UNIT TAG:

ORDER NUMBER:

DATE:

ENGINEER:

SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



CRSD-HV

Coalescing medium style sediment separator with removable head for high velocity applications

DESCRIPTION

The Bell & Gossett CRSD-HV is a sediment separator that utilizes a coalescing medium to remove impurities from high velocity HVAC systems. It features a stainless steel coalescing medium with 58% open area, removable end cover for coalescing medium access, and connections for an air vent, blow down valve, and skim valve. The product is designed, constructed, inspected and stamped per ASME Section VIII, Division 1.

CONSTRUCTION MATERIALS

Shell: Carbon Steel

Coalescing Medium: Stainless Steel

OPERATING DATA*

Max Working Pressure: 150 psig (1,034 kPa)


Max Temperature: 450°F (232°C)

Min Temperature: -20°F (-29°C)

* Consult factory for higher working pressures or temperatures.

SCHEDULE

PART NUMBER	MODEL NUMBER	INLET/OUTLET CONNECTION	RECOMMENDED CAPACITY IN GPM (M ³ /HR)	TAGGING INFORMATION	QUANTITY
5338-14F-15-002	CRSD-14F-HV	14" Flanged	4,625 (1,050)		
5338-14G-15-002	CRSD-14G-HV	14" Grooved	4,625 (1,050)		
5338-16F-15-002	CRSD-16F-HV	16" Flanged	5,785 (1,315)		
5338-16G-15-002	CRSD-16G-HV	16" Grooved	5,785 (1,315)		
5338-18F-15-002	CRSD-18F-HV	18" Flanged	7,460 (1,695)		
5338-18G-15-002	CRSD-18G-HV	18" Grooved	7,460 (1,695)		
5338-20F-15-002	CRSD-20F-HV	20" Flanged	8,950 (2,035)		
5338-20G-15-002	CRSD-20G-HV	20" Grooved	8,950 (2,035)		
5338-22F-15-002	CRSD-22F-HV	22" Flanged	10,855 (2,465)		
5338-22G-15-002	CRSD-22G-HV	22" Grooved	10,855 (2,465)		
5338-24F-15-002	CRSD-24F-HV	24" Flanged	13,050 (2,965)		
5338-24G-15-002	CRSD-24G-HV	24" Grooved	13,050 (2,965)		




DIMENSIONS AND WEIGHTS

MODEL NUMBER	DIMENSIONS - INCHES (mm)										SHIPPING WEIGHT LBS (KG)	FLOODED WEIGHT LBS (KG)	CV
	A	B	C	D	E	F	G	H	J	K			
CRSD-14F-HV	77.50 (1969)	54.00 (1372)	45.00 (1143)	33.00 (838)	28.00 (711)	12.50 (318)	3/4" NPT	1/2" NPT	2" NPT	6.50 (165)	1369 (621)	3007 (1364)	2,362
CRSD-16F-HV	77.50 (1969)	54.00 (1372)	50.00 (1270)	37.00 (940)	32.00 (813)	12.50 (318)	3/4" NPT	1/2" NPT	2" NPT	6.50 (165)	1641 (745)	3797 (1723)	3,255
CRSD-18F-HV	84.00 (2134)	54.00 (1372)	56.00 (1422)	42.00 (1067)	36.00 (914)	12.50 (318)	3/4" NPT	1/2" NPT	2" NPT	8.50 (216)	2077 (943)	4926 (2235)	4,048
CRSD-20F-HV	89.00 (2261)	54.00 (1372)	61.50 (1562)	46.00 (1168)	40.00 (1016)	14.00 (356)	3/4" NPT	1/2" NPT	2" NPT	5.50 (140)	2589 (1175)	6314 (2864)	5,049
CRSD-22F-HV	90.00 (2286)	54.00 (1372)	62.00 (1575)	53.00 (1346)	48.00 (1219)	15.50 (394)	3/4" NPT	1/2" NPT	2" NPT	5.50 (140)	3148 (1428)	8394 (3808)	6,216
CRSD-24F-HV	90.00 (2286)	54.00 (1372)	62.00 (1575)	53.00 (1346)	48.00 (1219)	15.50 (394)	3/4" NPT	1/2" NPT	2" NPT	5.50 (140)	3210 (1457)	8556 (3881)	8,234

IMPORTANT NOTES

- 1. Consult IOM 0121-01 for safety and service instructions.
- 2. Lifting lugs are for transportation and installation of the empty vessel, and are not to be used for complete or partial support of the flooded vessel.
- 3. Welding to the pressure vessel boundary will void the ASME stamp.
- 4. Dimensions subject to change. Not to be used for construction purposes.




DIMENSIONS AND WEIGHTS

MODEL NUMBER	DIMENSIONS - INCHES (mm)										SHIPPING WEIGHT LBS (KG)	FLOODED WEIGHT LBS (KG)	CV
	A	B	C	D	E	F	G	H	J	K			
CRSD-14G-HV	77.50 (1969)	54.00 (1372)	45.00 (1143)	33.00 (838)	28.00 (711)	12.50 (318)	3/4" NPT	1/2" NPT	2" NPT	6.50 (165)	1219 (553)	2865 (1300)	2,362
CRSD-16G-HV	77.50 (1969)	54.00 (1372)	50.00 (1270)	37.00 (940)	32.00 (813)	12.50 (318)	3/4" NPT	1/2" NPT	2" NPT	6.50 (165)	1445 (656)	3616 (1641)	3,255
CRSD-18G-HV	84.00 (2134)	54.00 (1372)	56.00 (1422)	42.00 (1067)	36.00 (914)	12.50 (318)	3/4" NPT	1/2" NPT	2" NPT	8.50 (216)	1863 (846)	4735 (2148)	4,048
CRSD-20G-HV	89.00 (2261)	54.00 (1372)	61.50 (1562)	46.00 (1168)	40.00 (1016)	14.00 (356)	3/4" NPT	1/2" NPT	2" NPT	5.50 (140)	2319 (1052)	6118 (2776)	5,049
CRSD-22G-HV	90.00 (2286)	54.00 (1372)	62.00 (1575)	53.00 (1346)	48.00 (1219)	15.50 (394)	3/4" NPT	1/2" NPT	2" NPT	5.50 (140)	2824 (1281)	8069 (3661)	6,216
CRSD-24G-HV	90.00 (2286)	54.00 (1372)	62.00 (1575)	53.00 (1346)	48.00 (1219)	15.50 (394)	3/4" NPT	1/2" NPT	2" NPT	5.50 (140)	2824 (1281)	8242 (3739)	8,234

IMPORTANT NOTES

- 1. Consult IOM 0121-01 for safety and service instructions.
- 2. Lifting lugs are for transportation and installation of the empty vessel, and are not to be used for complete or partial support of the flooded vessel.
- 3. Welding to the pressure vessel boundary will void the ASME stamp.
- 4. Dimensions subject to change. Not to be used for construction purposes.



Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Tel: (847) 966-3700 Fax: (847) 965-8379
www.xylem.com/bellgossett