


JOB:	REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:
ENGINEER:	SUBMITTED BY:	DATE:
CONTRACTOR:	APPROVED BY:	DATE:



Model VSC

10x12x10¹/₂A

Double Suction Split Case Pump



SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

STANDARD MATERIALS OF CONSTRUCTION


- Cast Iron Bronze Fitted
- Heavy Duty Maintenance Free Bearings
- Alignment Friendly Coupling
- Heavy Duty Groutless Baseplate
- ANSI/OSHA Coupling Guard
- ISO 1940-1:2003 Impeller Balance


OPTIONAL MATERIALS OF CONSTRUCTION

- Galvanized Drip Pan
- Spacer Coupling

TYPE OF SEAL AND WORKING PRESSURE

- Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 200 PSIG (13.7 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)






FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	10"	2.125 (54)	17.00 (432)
Suction	12"	2.25 (57)	20.25 (514)

FLANGES ARE 125# ANSI - STANDARD
250# ANSI - AVAILABLE

DIMENSIONS IN INCHES (MM)		
S	X	Z
9.82 (249)	19 (483)	9.82 (249)

Removal clearance from end of bracket: 26 Inches (660 mm)



*Motor dimensions are approximate and vary by manufacturer and motor type.


**Distance to the next available hole.

MOTOR FRAME	DIMENSIONS - INCHES (mm) FOR STANDARD COUPLER															
	CP	HA	HB	HC	HD	2HE	HF ₁	HF ₂ **	HG	HH	HM	HO	HP	HQ	HR	W
286T/TS	37.9 (963)	31.4 (798)	73 (1854)	66.33 (1685)	27.25 (692)	29.52 (750)	63 (1600)	15.75 (400)	6.25 (159)	0.88 (22)	35.07 (891)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
324T/TS	37.9 (963)	31.4 (798)	73 (1854)	69.15 (1756)	27.25 (692)	29.52 (750)	63 (1600)	15.75 (400)	6.25 (159)	0.88 (22)	35.82 (910)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
326T/TS	37.9 (963)	31.4 (798)	73 (1854)	70.27 (1785)	27.25 (692)	29.52 (750)	63 (1600)	15.75 (400)	6.25 (159)	0.88 (22)	36.35 (923)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
364T/TS	37.9 (963)	31.4 (798)	73 (1854)	72.11 (1832)	27.25 (692)	29.52 (750)	63 (1600)	15.75 (400)	6.25 (159)	0.88 (22)	37.2 (945)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
365T/TS	37.9 (963)	31.4 (798)	73 (1854)	72.11 (1832)	27.25 (692)	29.52 (750)	63 (1600)	15.75 (400)	6.25 (159)	0.88 (22)	37.2 (945)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
404T/TS	37.9 (963)	31.4 (798)	73 (1854)	75.21** (1910)	27.25 (692)	29.52 (750)	63 (1600)	15.75 (400)	6.25 (159)	0.88 (22)	37.72 (958)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
405T/TS	37.9 (963)	31.4 (798)	73 (1854)	77.21** (1961)	27.25 (692)	29.52 (750)	63 (1600)	15.75 (400)	6.25 (159)	0.88 (22)	37.72 (958)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
444T/TS	37.9 (963)	31.4 (798)	84 (2134)	82.68 (2100)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	42.77 (1086)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
445T/TS	37.9 (963)	31.4 (798)	84 (2134)	84.28 (2141)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	42.77 (1086)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
447T/TS	37.9 (963)	31.4 (798)	84 (2134)	90.76 (2305)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	41.13 (1045)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
449T/TS	37.9 (963)	31.4 (798)	84 (2134)	91.46 (2323)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	41.13 (1045)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Units may be built where foot/feet overhang the motor mounting platform. If overhang is unacceptable, consult factory for a custom submittal, quotation and/or lead time. A certified motor drawing will be required.

JOB:	REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:
ENGINEER:	SUBMITTED BY:	DATE:
CONTRACTOR:	APPROVED BY:	DATE:



Model VSC

10x12x10¹/₂A

Double Suction Split Case Pump



SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

STANDARD MATERIALS OF CONSTRUCTION


- Cast Iron Bronze Fitted
- Heavy Duty Maintenance Free Bearings
- Alignment Friendly Coupling
- Heavy Duty Groutless Baseplate
- ANSI/OSHA Coupling Guard
- ISO 1940-1:2003 Impeller Balance

OPTIONAL MATERIALS OF CONSTRUCTION


- Galvanized Drip Pan
- Spacer Coupling

TYPE OF SEAL AND WORKING PRESSURE

- Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 200 PSIG (13.7 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)



JOB:	REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:
ENGINEER:	SUBMITTED BY:	DATE:
CONTRACTOR:	APPROVED BY:	DATE:



Model VSC

10x12x10¹/₂A

Double Suction Split Case Pump



SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

STANDARD MATERIALS OF CONSTRUCTION


- Cast Iron Bronze Fitted
- Heavy Duty Maintenance Free Bearings
- Alignment Friendly Coupling
- Heavy Duty Groutless Baseplate
- ANSI/OSHA Coupling Guard
- ISO 1940-1:2003 Impeller Balance


OPTIONAL MATERIALS OF CONSTRUCTION

- Galvanized Drip Pan
- Spacer Coupling

TYPE OF SEAL AND WORKING PRESSURE

- Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 200 PSIG (13.7 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)






FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	10"	2.125 (54)	17.00 (432)
Suction	12"	2.25 (57)	20.25 (514)

FLANGES ARE 125# ANSI - STANDARD
250# ANSI - AVAILABLE

DIMENSIONS IN INCHES (MM)		
S	X	Z
9.82 (249)	19 (483)	9.82 (249)

Removal clearance from end of bracket: 26 Inches (660 mm)



*Motor dimensions are approximate and vary by manufacturer and motor type.

**Distance to the next available hole.

MOTOR FRAME	DIMENSIONS - INCHES (mm) FOR SPACER COUPLER****															
	CP	HA	HB	HC	HD	2HE	HF ₁	HF ₂ **	HG	HH	HM	HO	HP	HQ	HR	W
286T/TS	37.9 (963)	31.40 (798)	84 (2134)	77.58 (1971)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	35.07 (891)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
324T/TS	37.9 (963)	31.40 (798)	84 (2134)	80.4 (2042)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	35.82 (910)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
326T/TS	37.9 (963)	31.40 (798)	84 (2134)	81.52 (2071)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	36.35 (923)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
364T/TS	37.9 (963)	31.40 (798)	84 (2134)	83.36 (2117)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	37.2 (945)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
365T/TS	37.9 (963)	31.40 (798)	84 (2134)	83.36 (2117)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	37.2 (945)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
404T/TS	37.9 (963)	31.40 (798)	84 (2134)	85.96** (2183)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	37.72 (958)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
405T/TS	37.9 (963)	31.40 (798)	84 (2134)	87.96** (2234)	27.25 (692)	29.52 (750)	74 (1880)	18.50 (470)	6.25 (159)	0.88 (22)	37.72 (958)	46.25 (1175)	5 (127)	5	9.125 (232)	20.82 (529)
444T/TS	37.9 (963)	31.40 (798)	94 (2388)	93.43 (2373)	27.25 (692)	29.52 (750)	84 (2134)	16.80 (427)	6.25 (159)	0.88 (22)	42.77 (1086)	46.25 (1175)	5 (127)	6	9.125 (232)	20.82 (529)
445T/TS	37.9 (963)	31.40 (798)	94 (2388)	95.03 (2414)	27.25 (692)	29.52 (750)	84 (2134)	16.80 (427)	6.25 (159)	0.88 (22)	42.77 (1086)	46.25 (1175)	5 (127)	6	9.125 (232)	20.82 (529)
447T/TS	37.9 (963)	31.40 (798)	94 (2388)	101.51 (2578)	27.25 (692)	29.52 (750)	84 (2134)	16.80 (427)	6.25 (159)	0.88 (22)	41.13 (1045)	46.25 (1175)	5 (127)	6	9.125 (232)	20.82 (529)
449T/TS	37.9 (963)	31.40 (798)	94 (2388)	102.21 (2596)	27.25 (692)	29.52 (750)	84 (2134)	16.80 (427)	6.25 (159)	0.88 (22)	41.13 (1045)	46.25 (1175)	5 (127)	6	9.125 (232)	20.82 (529)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Units may be built where foot/feet overhang the motor mounting platform. If overhang is unacceptable, consult factory for a custom submittal, quotation and/or lead time. A certified motor drawing will be required.

****These dimensions are valid when using the Woods Duraflex spacer coupling option. For dimensions on Falk SteelFlex coupling options, consult factory for a special submittal drawing.

Fax: (847)965-8379
www.bellgossett.com

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2013 Xylem Inc.