




Bell & Gossett
a xylem brand

SUBMITTAL

B-880.5B

JOB:		REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:	
ENGINEER:	SUBMITTED BY:	DATE:	
CONTRACTOR:	APPROVED BY:	DATE:	



2AD Series e-1510 Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- ☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling






Bell & Gossett
a xylem brand

SUBMITTAL

B-880.5B

JOB:		REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:	
ENGINEER:	SUBMITTED BY:	DATE:	
CONTRACTOR:	APPROVED BY:	DATE:	



2AD Series e-1510 Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- ☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling





Bell & Gossett
a xylem brand

SUBMITTAL

B-880.5B

JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:


SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



2AD Series e-1510 Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- ☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL


- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling



Series e-1510 2AD Centrifugal Pump Submittal

B-880.5B



FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	2"	5/8" (16)	6" (152)
Suction	2-1/2"	11/16" (17)	7-1/8" (181)

FLANGES ARE 125# ANSI - STANDARD

DIMENSIONS – Inches (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"S" FRAME														
56	12 (305)	28-3/4 (730)	28-7/8 (733)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	–	3/4 (19)	3-9/16 (90)	13-3/8 (340)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
143T	12 (305)	28-3/4 (730)	29 (737)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	–	3/4 (19)	3-9/16 (90)	13-1/2 (343)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
145T	12 (305)	28-3/4 (730)	30 (762)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	–	3/4 (19)	3-9/16 (90)	13-1/2 (343)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
182T	14-5/8 (371)	31 (787)	32-5/8 (829)	9-3/4 (248)	12-7/8 (327)	25 (635)	–	3/4 (19)	2-3/16 (56)	15 (381)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
184T	14-5/8 (371)	31 (787)	33-3/8 (848)	9-3/4 (248)	12-7/8 (327)	25 (635)	–	3/4 (19)	2-3/16 (56)	15 (381)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
213T	14-5/8 (371)	34-5/8 (879)	36 (914)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	–	3/4 (19)	2-3/16 (56)	15-5/8 (397)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
215T	14-5/8 (371)	34-5/8 (879)	37-1/2 (953)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	–	3/4 (19)	2-3/16 (56)	15-5/8 (397)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
254T	14-5/8 (371)	39-3/8 (1000)	41-1/4 (1048)	10-3/4 (273)	12-7/8 (327)	33-3/8 (848)	–	3/4 (19)	2-3/16 (56)	17-5/8 (448)	17-1/4 (438)	3 (76)	3-1/2 (89)	4-3/4 (121)
256T	14-5/8 (371)	39-3/8 (1000)	43 (1092)	10-3/4 (273)	12-7/8 (327)	33-3/8 (848)	–	3/4 (19)	2-3/16 (56)	17-5/8 (448)	17-1/4 (438)	3 (76)	3-1/2 (89)	4-3/4 (121)

STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"S" FRAME														
56	14-5/8 (371)	34-5/8 (879)	32-3/8 (822)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	–	3/4 (19)	2-3/16 (56)	13-3/8 (340)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
143T	14-5/8 (371)	34-5/8 (879)	32-1/2 (826)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	–	3/4 (19)	2-3/16 (56)	13-1/2 (343)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
145T	14-5/8 (371)	34-5/8 (879)	33-1/2 (851)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	–	3/4 (19)	2-3/16 (56)	13-1/2 (343)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
182T	14-5/8 (371)	34-5/8 (879)	36-1/4 (921)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	–	3/4 (19)	2-3/16 (56)	15 (381)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
184T	14-5/8 (371)	34-5/8 (879)	37 (940)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	–	3/4 (19)	2-3/16 (56)	15 (381)	16-1/4 (413)	3 (76)	3-1/2 (89)	4-3/4 (121)
"L" FRAME														
213T	16 (406)	46-1/2 (1181)	42-3/4 (1086)	11 (279)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	3-5/16 (84)	16-7/8 (429)	17-1/2 (445)	5 (127)	3-1/2 (89)	4-3/4 (121)
215T	16 (406)	46-1/2 (1181)	44-1/4 (1124)	11 (279)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	3-5/16 (84)	16-7/8 (429)	17-1/2 (445)	5 (127)	3-1/2 (89)	4-3/4 (121)
254T	16 (406)	51-3/4 (1314)	48 (1219)	12 (305)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-5/16 (84)	18-7/8 (479)	18-1/2 (470)	5 (127)	3-1/2 (89)	4-3/4 (121)
256T	16 (406)	51-3/4 (1314)	49-3/4 (1264)	12 (305)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	3-5/16 (84)	18-7/8 (479)	18-1/2 (470)	5 (127)	3-1/2 (89)	4-3/4 (121)

Dimensions are subject to change. Not to be used for construction purposes unless certified.



Xylem Inc.
8200 N. Austin Avenue, Morton Grove, IL 60053
Phone: (847)966-3700 Fax: (847)965-8379
www.bellgossett.com
Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2016 Xylem Inc.