


JOB: REPRESENTATIVE:

UNIT TAG: ORDER NO. DATE:
ENGINEER: SUBMITTED BY: DATE:
CONTRACTOR: APPROVED BY: DATE:



6BD Series e-1531 Close-Coupled Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____
HP _____ RPM _____
VOLTS _____
CYCLE _____ PHASE _____
ENCLOSURE _____
APPROX. WEIGHT _____
SPECIALS _____

MATERIALS OF CONSTRUCTION


☒ STAINLESS STEEL FITTED

MAXIMUM WORKING PRESSURE

☒ 175 psi (12 bar) W.P.


TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
☐ -S Stuffing Box construction w/ Flushed Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
☐ -PF Stuffing Box Construction
w/ Flushed Packing
(Graphite Impregnated Teflon)



JOB: REPRESENTATIVE:

UNIT TAG: ORDER NO. DATE:
ENGINEER: SUBMITTED BY: DATE:
CONTRACTOR: APPROVED BY: DATE:



6BD Series e-1531 Close-Coupled Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____
HP _____ RPM _____
VOLTS _____
CYCLE _____ PHASE _____
ENCLOSURE _____
APPROX. WEIGHT _____
SPECIALS _____

MATERIALS OF CONSTRUCTION


☒ STAINLESS STEEL FITTED


MAXIMUM WORKING PRESSURE

☒ 175 psi (12 bar) W.P.

TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
☐ -S Stuffing Box construction w/ Flushed Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
☐ -PF Stuffing Box Construction
w/ Flushed Packing
(Graphite Impregnated Teflon)





SIZE OF PUMP AND DISCHARGE	SUCTION	PUMP DIMENSIONS IN INCHES (MM)			
		DD	X	Y	Z
6BD	8	10.375 (264)	10.5 (267)	7 (178)	8.25 (210)

125# ANSI FLANGE DIMENSIONS - INCHES (MM)				
PIPE SIZE OF FLANGE	O.D. OF FLANGE	DIA. OF BOLT CIRCLE	NO. OF BOLTS	SIZE OF BOLTS
6	12.125 (308)	9.5 (241)	8	0.75 (19)
8	14.75 (375)	11.75 (298)	8	0.75 (19)

DIMENSIONS – Inches (mm)

STANDARD SEAL

MOTOR FRAME	A (Max)	AB (Max)	B (Max)	CP (Max)	D	2E	F	H	L	O (Max)
254JM	12.5 (318)	10.75 (273)	10.75 (273)	35 (889)	6.25 (159)	10 (254)	8.25 (210)	0.531 (13)	19.375 (493)	13.125 (333)
256JM	12.5 (318)	10.75 (273)	12.5 (318)	36.75 (934)	6.25 (159)	10 (254)	10 (254)	0.531 (13)	19.375 (493)	13.125 (333)
284JM	14 (356)	12.625 (321)	12.5 (318)	36.125 (918)	7 (178)	11 (279)	9.5 (241)	0.531 (13)	19.375 (493)	15 (381)
286JM	14 (356)	12.625 (321)	14 (356)	37.625 (950)	7 (178)	11 (279)	11 (279)	0.531 (13)	19.375 (493)	15 (381)
324JM	16 (406)	15.125 (384)	14 (356)	39.125 (994)	8 (203)	12.5 (318)	10.5 (267)	0.656 (17)	19.375 (493)	17 (432)
326JM	16 (406)	15.125 (384)	15.5 (394)	40.625 (1032)	8 (203)	12.5 (318)	12 (305)	0.656 (17)	19.875 (505)	17 (432)

STUFFING BOX

MOTOR FRAME	A (Max)	AB (Max)	B (Max)	CP (Max)	D	2E	F	H	L	O (Max)
254JP	12.5 (318)	10.75 (273)	10.75 (273)	37.875 (962)	6.25 (159)	10 (254)	8.25 (210)	0.531 (13)	22.25 (565)	13.125 (333)
256JP	12.5 (318)	10.75 (273)	12.5 (318)	39.625 (1006)	6.25 (159)	10 (254)	10 (254)	0.531 (13)	22.25 (565)	13.125 (333)
284JP	14 (356)	12.625 (321)	12.5 (318)	39 (991)	7 (178)	11 (279)	9.5 (241)	0.531 (13)	22.25 (565)	15 (381)
286JP	14 (356)	12.625 (321)	14 (356)	40.5 (1029)	7 (178)	11 (279)	11 (279)	0.531 (13)	22.25 (565)	15 (381)
324JP	16 (406)	15.125 (384)	14 (356)	42 (1067)	8 (203)	12.5 (318)	10.5 (267)	0.656 (17)	22.75 (578)	17 (432)
326JP	16 (406)	15.125 (384)	15.5 (394)	43.5 (1105)	8 (203)	12.5 (318)	12 (305)	0.656 (17)	22.75 (578)	17 (432)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.bellgossett.com

xylem
Let's Solve Water

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2015 Xylem Inc.