

JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:

SUBMITTED BY:

DATE:

CONTRACTOR:



APPROVED BY:

DATE:



SUPPORT LEGS

Heat Transfer Products



DIMENSIONS & WEIGHTS

PART NUMBER	SHELL DIA.	LEG DIMENSIONS INCHES (MM)					APPROX. SHIP. WGT. Lbs. (Kg) (per pair)
		A	B	C	D	E	
1-147-7-04-210-01	4 (102)	7 (178)	5-1/2 (140)	4-13/16 (122)	3/4 (19)	2-1/2 (64)	5 (2.3)
1-147-7-06-210-01	6 (152)	8-1/8 (206)	6-3/4 (171)	6-11/16 (170)	3/4 (19)	2-1/2 (64)	6 (2.7)
1-147-7-08-210-01	8 (203)	10-3/8 (264)	9 (229)	7 (178)	3/4 (19)	2-1/2 (64)	8 (3.6)
1-147-7-10-210-01	10 (254)	11-1/8 (283)	9-5/8 (244)	9-3/8 (238)	7/8 (22)	2-1/2 (64)	11 (5)
1-147-7-12-210-01	12 (305)	13-1/8 (333)	11-5/8 (295)	9-3/4 (248)	7/8 (22)	2-1/2 (64)	13 (5.9)
1-147-7-14-210-01	14 (356)	14-3/8 (365)	12-1/2 (318)	11-5/8 (295)	1 (25)	3 (76)	24 (10.9)
1-147-7-16-210-01	16 (406)	16-1/2 (419)	14-5/8 (371)	12 (305)	1 (25)	3 (76)	30 (13.6)
1-147-7-18-210-01	18 (457)	18-1/2 (470)	16 (406)	13-5/8 (346)	1-1/8 (29)	3 (76)	36 (16.3)
1-147-7-20-210-01	20 (508)	20-1/2 (521)	18 (457)	14 (356)	1-1/8 (29)	3 (76)	42 (19.1)
1-147-7-24-210-01	24 (610)	24-3/4 (629)	22-1/4 (565)	14-3/4 (375)	1-1/8 (29)	3 (76)	50 (22.7)

PART NUMBER	SHELL DIA.	LEG DIMENSIONS INCHES (MM)					APPROX. SHIP. WGT. Lbs. (Kg) (per pair)
		A	B	C	D	E	
4-540-16-303-001	16 (406)	16-1/2 (419)	14-5/8 (371)	12 (305)	1 (25)	3 (76)	32 (14.5)
4-540-18-303-001	18 (457)	18-1/2 (470)	16 (406)	13-5/8 (346)	1-1/8 (29)	3 (76)	40 (18.1)
4-540-20-303-001	20 (508)	20-1/2 (521)	18 (457)	14 (356)	1-1/8 (29)	3 (76)	50 (22.7)
4-540-22-303-001	22 (559)	22-1/2 (572)	20 (508)	14-1/2 (368)	1-1/8 (29)	3 (76)	55 (24.9)
4-540-24-303-001	24 (610)	24-3/4 (629)	22-1/4 (565)	14-3/4 (375)	1-1/8 (29)	3 (76)	58 (26.3)
4-540-26-303-001	26 (660)	26-1/2 (673)	24 (610)	15-3/4 (400)	1-1/8 (29)	3 (76)	62 (28.1)
4-540-28-303-001	28 (711)	28-1/2 (724)	26 (660)	16-3/4 (425)	1-1/8 (29)	3 (76)	72 (32.7)
4-540-30-303-001	30 (762)	30-3/4 (781)	28-1/4 (718)	17-3/4 (451)	1-1/8 (29)	3 (76)	78 (35.4)


CAUTION:Type "BLZ" and "Strap Cradles" should not be used for ceiling suspension or vertical wall Mounting of heat exchangers.

NOTE: Support legs are OPTIONAL and will be furnished only as a separate item on order (give size and type).

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.bellgossett.com

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2015 Xylem Inc.

xylem
Let's Solve Water



Cast Steel Cradles

SHELL DIA.	LEG DIMENSIONS IN INCHES (MM)									PART NUMBER	APPROX. SHIP. WGT. IN LBS.(Kg) (PER PAIR)
	A	B	C	D	E	F	G	H	J		
4	4-1/8 (105)	4 (102)	2-1/4 (57)	2-1/2 (64)	1-3/8 (35)	5/16 (8)	5/8 x 7/8 (16 x 22)	N/A	2-1/4 (57)	1-147-5-05-210-01	6 (2.7)
5	4-3/4 (121)	4 (102)	2-1/4 (57)	2-1/2 (64)	1-3/8 (35)	5/16 (8)	5/8 x 7/8 (16 x 22)	2-25/32 (71)	NA	1-147-5-05-210-01	6 (2.7)
6	5-1/4 (133)	6 (152)	2-1/4 (57)	4-1/2 (114)	1-3/8 (35)	5/16 (8)	5/8 x 7/8 (16 x 22)	NA	3-5/16 (84)	1-147-5-08-210-01	7 (3.2)
8	6-1/2 (165)	6 (152)	2-1/4 (57)	4-1/2 (114)	1-3/8 (35)	5/16 (8)	5/8(16) x 7/8(22)	4-5/16 (110)	NA	1-147-5-08-210-01	7 (3.2)
10	7-1/2 (190)	8 (203)	2-1/4 (57)	5-1/2 (140)	1-3/8 (35)	3/8 (10)	5/8 x 7/8 (16 x 22)	5-3/8 (137)	NA	1-147-5-10-210-01	9 (4.1)
12	8-1/2 (216)	9 (229)	2..25 (83)	6-1/2 (165)	1-3/8 (35)	3/8 (10)	5/8 x 7/8 (16 x 22)	6-3/8 (162)	NA	1-147-5-12-210-01	11 (5)
14	10-1/2 (267)	9-3/4 (248)	3-1/4 (83)	7-1/2 (190)	2 (51)	3/8 (10)	3/4 x 1-1/4 (19 x 32)	7 (178)	NA	1-147-5-13-210-01	20 (9.1)
16	11-1/2 (292)	13/4 (273)	3-1/4 (83)	8-1/2 (216)	2 (51)	3/8 (10)	3/4 x 1-1/4 (19 x 32)	8 (203)	NA	1-147-5-15-210-01	23 (10.4)
18	12 (305)	11-3/4 (298)	3-1/4 (83)	9-1/2 (241)	2 (51)	3/8 (10)	3/4 x 1-1/4 (19 x 32)	9 (229)	NA	1-147-5-17-210-01	24 (10.9)
20	13 (330)	12-3/4 (324)	4 (102)	10-1/2 (267)	2-3/4 (70)	1/2 (13)	3/4 x 1-1/4 (19 x 32)	10 (254)	NA	1-147-5-19-210-01	33 (15)
22	13-11/16 (348)	15-1/2 (394)	4 (102)	13-1/2 (343)	2-3/4 (70)	1/2 (13)	3/4 x 1-1/4 (19 x 32)	NA	10-7/8 (276)	1-147-5-23-210-01	46 (20.9)
24	15 (381)	15-1/2 (394)	4 (102)	13-1/2 (343)	2-3/4 (70)	1/2 (13)	3/4 x 1-1/4 (19 x 32)	12 (305)	NA	1-147-5-23-210-01	46 (20.9)

MATERIAL: CAST STEEL A27-NI
NOTE: Cast steel cradles can be factory welded to the heat exchanger at additional cost.
CAUTION: Field welding negate the ASME stamp of the heat exchanger or pressure vessel.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.bellgossett.com
Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2015 Xylem Inc.

