




Job	Representative	
Unit tag	Order number	Date
Engineer	Submitted by	Date
Contractor	Approved by	Date



Circuit Setter®

Calibrated balance valves
with grooved connections

Description

The Bell & Gossett Circuit Setter calibrated balance valve is a precision machined triple purpose balancing instrument. It is precisely calibrated for use as a presettable balance valve, variable orifice flow meter and positive shut-off service valve.

Valves are furnished with a calibrated nameplate and memory stop indicator which permits the value to be preset to a fixed open position and then closed for service without disturbing valve setting.

Valves are equipped with capped readout valves fitted with internal check valves.

Maximum operating temperature: 250°F (121°C)

Maximum working pressure: 300 PSIG (2068 kPa)

Sizes 4"-12"

Body & bonnet - grooved: ductile iron

Disc: 4" - 8" brass with EPDM insert

10" - 12" stainless steel with EPDM insert

Stern: stainless steel

Packing: teflon-graphite (asbestos-free)

Gasket: synthetic fiber - nitrile binder (asbestos-free)


Seal ring: EPDM

Bushing: nickel plated steel

Schedule

Model no.	Part no.	Tagging information	Quantity
CB-4G	117476		
CB-5G	116477		
CB-6G	117478		
CB-8G	117479		
CB-10G	117641		
CB-12G	117642		

Circuit Setter calibrated balance valves



Dimensions and weights*

Dimensions in inches (MM)

Model no.	Pipe size	Conns.	A		B	C	D		E	Max. Width of valve	Weight in lbs. (kg)
			Open	Closed			Open	Closed			
CB-4G	4 (101.6)	GRVD.	14-5/8 (371.5)	13-5/8 (346.1)	15-1/8 (384.2)	2-1/4 (57.2)	15-11/16 (424.0)	13-15/16 (354.0)	6-1/4 (158.8)	9 (254.0)	70 (32)
CB-5G	5 (127)	GRVD.	16-9/32 (413.5)	15-1/32 (407.2)	17-1/8 (435.0)	2-25/32 (70.6)	17-11/32 (440.5)	15-9/16 (395.3)	6-7/8 (174.6)	10 (254.0)	86 (39)
CB-6G	6 (152.4)	GRVD.	18-9/16 (471.5)	17-1/16 (433.4)	19 (482.6)	3-5/16 (84.1)	19-1/2 (495.3)	17-13/32 (442.1)	8-1/4 (209.6)	11 (279.4)	160 (73)
CB-8G	8 (203.2)	GRVD.	22-5/16 (566.7)	20-13/16 (528.6)	22-1/2 (571.5)	3-5/16 (84.1)	22-3/8 (568.3)	20-5/16 (516.0)	10-3/8 (263.5)	14-1/4 (362.0)	270 (123)
CB-10G	10 (254)	GRVD.	26-1/4 (666.8)	23-7/8 (606.4)	26-1/2 (673.1)	5-3/8 (136.5)	26-1/32 (661.2)	23-3/16 (589.0)	12-1/4 (311.2)	17 (431.8)	384 (174)
CB-12G	12 (304.8)	GRVD.	30-3/8 (771.5)	28 (711.2)	31 (787.4)	6-3/8 (161.9)	30-7/16 (773.1)	26-15/16 (684.2)	14-1/2 (368.3)	20 (508.0)	546 (248)

All dimensions are +/- 0.125" (3.2 mm) tolerance. Dimensions are subjected to change. Not to be used for construction purposes unless certified.

Important


When monitoring system flow, care must be exercised to avoid direct skin or eye contact with liquids that may escape. Liquids with temperatures in excess of 120°F (49°C) may cause burns.

Bell & Gossett Circuit Setter balance valves are not recommended for use with meter connections pointing downward.

To retain calibrated accuracy, a minimum length of unrestricted straight pipe adjacent to the valve should be maintained as follows:

Size inches (mm)	Upstream "A" (in pipe diameters)	Downstream "B" (in pipe diameters)
4"-12" (101.6-304.8)	5	2

Best use results maximize straight pipe length entering and leaving valve. Obstructions or changes in planar flow profiles entering valve may affect accuracy if too close to valve.



Learn more
about Circuit
Setter Plus:



Xylem
8200 N. Austin Avenue
Morton Grove, IL 60053

Tel +1 847.966.3700
Fax +1 847.965.8379
xylem.com/bellgossett

This information is subject to revision without notice. Users are responsible for evaluating suitability for specific applications. Xylem makes no implied warranties including without limitation warranties as to fitness for a particular purpose. Xylem makes no representation regarding the completeness or accuracy of this information and is not liable for any direct or indirect damages arising from or relating to this information or its use.

© 2025 Xylem Inc. or its affiliate. All rights reserved. Bell & Gossett is a trademark of Xylem or one of its subsidiaries. All other trademarks or registered trademarks are the property of their respective owners.

A-547L 8/2025

xylem
Let's Solve Water