


JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



70M Series Simplex Pressure Booster System

DESIGN DATA:

System Capacity:		GPM
Pressure Required @ Discharge Header:		PSIG
Pressure Drop through Package (include PRV):		PSIG
Minimum Suction Pressure:		PSIG

PUMP DATA:


Series:	1510	Size	
Gallons Per Minute:			
Pump TDH (feet)			
PRV Size			
Motor HP furnished:			
Motor RPM:		Voltage	Hertz
			Phase

**STANDARD
EQUIPMENT:**

Basic unit fully piped, wired, tested and mounted on steel frame. Includes bronze-fitted B&G Series 1510 pump and motor, suction and discharge gauges, combination pressure reducing and nonslam check valve. Starter panel with fused disconnect, hand-off-auto and low suction cut-out.

**OPTIONAL
EQUIPMENT:**

Control Panel
☐ Yes ☐ Microprocessor Panel (See Submittal D-216)
☐ No ☐ Simplex MiniBooster Panel



Dimensions (inches)	A	B	C*
Maximum	62	30	55
Minimum	30	24	45

*Applicable to units with optional control panel.

Consult factory for unit dimension with a combined horsepower over 100.
 "Do not use for construction. Dimensions are approximate and subject to change.
 Contact factory for certified dimensions."